




[Positive Lock](#) | [Positive Lock 187](#)

TE Internal #: 170334-1

Quick Disconnects, Receptacle, 18 – 14 AWG Wire Size, .823 – 2.081 mm² Wire Size, 1624 – 4107 CMA Wire Size, Positive Lock 187

[View on TE.com >](#)

Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1624 – 4107 CMA**

Mating Tab Width: **6.35 mm [.25 in]**

Features

Product Type Features

Terminates To	Wire & Cable
Wire Stop	No
Wire/Cable Type	Regular Wire
Insertion Force	Low
Sealable	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open



Mechanical Attachment

Mating Retention Type	Dimple
Extraction Force	7 – 100 Newton
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.2 – 3.4 mm [.086 – .134 in]
Overall Length	25.8 mm [1.015 in]
Wire Size	1624 – 4107 CMA

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]

Industry Standards

UL Rating	Recognized
-----------	------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 172076-6
POSITIVE LOCK 250 HOUSING RECEPTACLE




TE Part # 172076-1
POSITIVE LOCK 250 HOUSING RECEPTACLE



TE Part # 2-172076-1
250 HSG. PL MKII REC. NAT



TE Part # 724659-2
EXT TOOL FOR POSITIVE .250



TE Part # 2-172076-6
PL 250 REC HSG 1P NYLON BLUE



TE Part # 2-172076-7
POSITIVE LOCK 250 HOUSING RECEPTACLE



TE Part # 172076-2
PL MKII 250 REC HSG 1P NYLON BLACK



TE Part # 2-172076-2
POSITIVE LOCK 250 HOUSING RECEPTACLE



TE Part # 178833-1
POSITIVE LOCK .250 HOUSING RECEPTACLE



TE Part # 177627-1
PL .250 (6.3 MM) HOUSING RECEPTACLE




TE Part # 172076-7
PL MKII 250 REC HSG 1P NYLON RED



TE Part # 174429-1
PL 250 HOUSING RECEPTACLE




TE Part # 177627-7
PL .250 (6.3 MM) HOUSING RECEPTACLE



TE Part # 172076-4
POSITIVE LOCK 250 HOUSING RECEPTACLE






TE Part # 172076-5
POSITIVE LOCK 250 HOUSING RECEPTACLE



TE Part # 2-172076-4
250 POSITIVE LOCK REC 1P YELL.



Also in the Series | Positive Lock 187



Documents

Product Drawings

[205 PL MII,REC.,18-14,PTBR](#)

Japanese

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_170334-1_S.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_170334-1_S.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_170334-1_S.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English



Product Compliance

English