

1757829-1 ✓ ACTIVE

## AMPLIMITE

TE Internal #: 1757829-1

Box Mount D-Sub Connectors, Plug, Post Diameter .76 mm [.03 in],

Vertical, Cable-to-Board, 9 Position, Size 1, Pin, Size 20

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors



Connector & Housing Type: **Plug**

Post Diameter: **.76 mm [.03 in]**

PCB Mount Orientation: **Vertical**

Connector System: **Cable-to-Board**

Number of Positions: **9**

### Features

#### Product Type Features

Product Type	Connector
Connector & Housing Type	Plug
Connector System	Cable-to-Board
D-Sub Shell Size	1
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Blindmate	No

#### Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	9
Power/Signal/Coax Combination	No

#### Body Features

Box Mount D-Sub Connector Insert Arrangement	MS18273-1
Shell Plating Material	Zinc
Shell Material	Steel
Non-Magnetic	No

#### Contact Features

Contact Type	Pin
Contact Mating Area Plating Material	Gold



Contact Base Material	Beryllium Copper, Brass
D-Sub Contact Size	20
Contact Current Rating (Max)	5 A

#### Termination Features

Termination Post Length	4.78 mm[.188 in]
-------------------------	------------------

#### Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
------------------------	-----------------

#### Housing Features

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------

#### Dimensions

Post Diameter	.76 mm[.03 in]
---------------	----------------

#### Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

#### Operation/Application

ULTRA-LITE Connector	No
Circuit Application	Signal

#### Industry Standards

NASA Qualification	No
--------------------	----

#### Packaging Features

Packaging Method	Package
------------------	---------

#### Other

Comment	"Z" is stamped on connectors following M24308 part number as required. "Z" designates zinc shell plating., For solder dip product see part number 1757829-6.
---------	--

#### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)



Candidate List Declared Against: JUL 2021  
(219)

SVHC > Threshold:

Pb (3.7% in Component)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Wave solder capable to 265°C

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Documents

### Product Drawings

[AMPLIMITE,PLUG ASY,POSTD,109,ZN,1](#)

English

### CAD Files

[3D PDF](#)

3D

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1757829-1\\_E.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1757829-1\\_E.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1757829-1\\_E.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Agency Approvals

[UL Report](#)

English