



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Panel, Wire-to-Wire**
Number of Positions: **4**
Centerline (Pitch): **4.2 mm [.165 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Multiple Contact Types	Without
Contact Retention Within Housing	Without
Contact Type	Pin



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Mounting Ears
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	4.2 mm[.165 in]
Housing Color	Natural
Housing Material	Nylon 6/6

Dimensions

Row-to-Row Spacing	4.2 mm[.163 in]
Panel Thickness	.8 – 2 mm[.031 – .078 in]

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
Insertion Force	3.9 kg

Operation/Application

Assembly Integration Feature	Without
Circuit Application	Power & Signal

Industry Standards

CSA Rating	Certified
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire
UL Rating	Recognized
Agency/Standard Number	E28476
CSA File Number	LR7189
VDE Tested	No
Agency/Standard	CSA, UL

Packaging Features

Packaging Method	Bag
Packaging Quantity	500



Other

For Use With	Mini-Universal MATE-N-LOK Plug Housing
--------------	--

Product Compliance





For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 1-770985-0 MINI UMNL PIN 26-22AWG AU LP	 TE Part # 1-770987-0 MINI UMNL PIN 22-18 AWG AU LP	 TE Part # 770988-3 MINI UMNL SOK 22-18AWG AU LP	 TE Part # 1-770988-0 MINI UMNL SOK 22-18AWG AU
---	--	---	--



 TE Part # 1-794059-0 MINI UMNL PIN L/P LF	 TE Part # 770988-1 MINI UMNL SOK 22-18AWG SN LP	 TE Part # 770986-1 MINI UMNL SOK 26-22AWG SN LP	 TE Part # 170365-3 MINI UNIVERSAL M-N-L SOCKET LP
 TE Part # 170364-3 MINI UNIVERSAL M-N-L PIN LP	 TE Part # 770985-1 MINI UMNL PIN 26-22AWG SN LP	 TE Part # 1-794407-1 MINI UMNL SOK 20-16 AWG AU LF	 TE Part # 170363-3 MINI UNIVERSAL M-N-L PIN LP
 TE Part # 172338-1 MINI UMNL PLUG HOUSING 4P	 TE Part # 171638-1 MINI U-M-N-L PIN CONT. L.P	 TE Part # 171639-1 MINI U-M-N-L SOCKET L.P	 TE Part # 770903-3 MINI UMNL PIN 22-18 AWG AU
 TE Part # 170364-1 MINI UNIVERSAL M-N-L PIN LP	 TE Part # 1-770902-1 MINI UMNL SOK 26-22 AWG AU LF	 TE Part # 170366-1 MINI UNIVERSAL M-N-L SOCKET LP	 TE Part # 170363-1 MINI UNIVERSAL M-N-L PIN LP

Also in the Series | Mini-Universal MATE-N-LOK

 Connector Contacts(11)	 Insertion & Extraction Tools(1)	 PCB Headers & Receptacles(1)	 Power Contacts(85)
---	---	---	---



Rectangular Backshells & Clamps(2)



Rectangular Boots & Strain Relief(2)



Rectangular Connector Keying Plugs(2)



Rectangular Connector Locking(2)



Rectangular Connector Seals(20)



Rectangular Power Connectors(283)

Documents

Product Drawings

MINI UNIVERSAL MATE-N-LOK CAP HOUSING 4P

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_172330-1_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_172330-1_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_172330-1_A1.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_172330-1_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_172330-1_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_172330-1_H.3d_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG](#)

English

[1-1773458-0_MINI_UNIVERSAL_MATE_N_LOK_CONNECTOR_SYSTEM_QRG](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_172330-1_0606201879_dmtec](#)

English

[MD_172330-1_0606201879_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[Agency Approval Document](#)

English

[Agency Approval Document](#)

English