




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Shield Case Kit**

Connector System: **Wire-to-Board**

Number of Positions: **100**

Shielded: **Yes**

Cable Exit Angle: **180° (In-Line)**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Shield Case Kit
Connector System	Wire-to-Board
Sealable	No

Configuration Features

Number of Positions	100
---------------------	-----

Body Features

Shield Plating Material	Nickel over Copper
Rear Shell Material	Steel
Rear Shell Plating Material	Nickel
Body Material	Glass-Filled Thermoplastic
Color	Beige White
Body Flammability Rating	UL 94V-0
Backshell Plating Material	Nickel over Copper
Backshell Material	Steel

Cable Exit Angle	180° (In-Line)
------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Shielded	Yes
----------	-----

Industry Standards

Locking Spring Flammability Rating	UL 94V-0
------------------------------------	----------

Cover Flammability Rating	UL 94V-0
---------------------------	----------

Packaging Features

Packaging Quantity	30
--------------------	----

Packaging Method	Box
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
--	--

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_176793-9_F.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_176793-9_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_176793-9_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

[Termination and Assy of CHAMP .050 Series \(II\) Shield Case Connector](#)

English

[Termination and Assy of CHAMP .050 Series \(II\) Shield Case Connector](#)

Japanese

[Application Specification](#)

Japanese