



Alcoswitch

TE Internal #: 1825095-1

Push Button Switches, Single Pole - Single Throw Configuration (Pole-Throw), Switch, Single Actuator, Flush Actuator Profile, Unthreaded

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Push Button Switches



Configuration (Pole-Throw): **Single Pole - Single Throw**

Push Button Switch Product Type: **Switch**

Number of Actuators: **Single**

Actuator Profile: **Flush**

Bushing Style: **Unthreaded**

Features

Product Type Features

Switch Type	Pushbutton
Dust Proof	No
Push Button Switch Product Type	Switch
Illuminated	No
Actuator Style	Rectangular

Configuration Features

ESD Grounding Terminal	Without
Ganged	No
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Tactile	Yes
Operating Function	Off (On)

Electrical Characteristics

Push Button Switch Voltage Rating	20 VDC
-----------------------------------	--------

Body Features

Seal Type	Terminal Seal (Epoxy)
-----------	-----------------------



Actuator Force	50 – 400 g[1.77 – 14.12 oz]
----------------	-----------------------------

Case Material	Thermoplastic (LCP)
---------------	---------------------

Actuator Material	Thermoplastic
-------------------	---------------

Actuator Profile	Flush
------------------	-------

Bushing Style	Unthreaded
---------------	------------

Actuator Color	Black
----------------	-------

Contact Features

Contact Base Material	Copper Alloy
-----------------------	--------------

Push Button Switch Contact Current Rating	.4 A
---	------

Switch Contact Plating Material	Gold
---------------------------------	------

Termination Features

Termination Type	Printed Circuit
------------------	-----------------

Mechanical Attachment

Mounting Angle	Vertical
----------------	----------

Push Button Switch Mounting Type	Through Hole
----------------------------------	--------------

Housing Features

Low Profile	No
-------------	----

Process Sealed	Yes
----------------	-----

Dimensions

Actuator Length	3.27 mm[.129 in]
-----------------	------------------

Button Width	3.81 mm[.15 in]
--------------	-----------------

Usage Conditions

Temperature Rating	Standard
--------------------	----------

Packaging Features

Packaging Method	Bulk
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	
--	--



Current ECHA Candidate List: JUNE 2022
(224)

Candidate List Declared Against: JAN 2021
(211)

Does not contain REACH SVHC

Halogen Content Not Yet Reviewed for halogen content

Solder Process Capability Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-1825097-1
TPBF11CGRA004



TE Part # 1825098-2
TPC11CGRA004



TE Part # 1825100-4
TPF11CGRA004



TE Part # 2-1825098-0
TPCF13C004



TE Part # 1-1825097-6
TPB11FGVRA004



TE Part # 1825096-4
TPA11CGRA004



TE Part # 1825097-6
TPB11CGRA004



TE Part # 1-1825096-0
TPA11FGRA004



Documents

Product Drawings

[TP11CGPC004](#)

English

Datasheets & Catalog Pages

[TP Series Data Sheet](#)

English