




Connectors > PCB Connectors > Board-to-Board Connectors > PCB Spring Contacts



Spring Finger Type: **Preloaded - C-Clip**

Scalable: **No**

Side Protected: **No**

Uncompressed Height: **1.8 mm [.071 in]**

Contact Length: **3.46 mm [.136 in]**

## Features

### Product Type Features

Spring Finger Type	Preloaded - C-Clip
Scalable	No
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Side Protected	No
Number of Positions	1

### Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Stainless Steel
Contact Length	3.46 mm [.136 in]
Contact Width	1 mm [.039 in]
Contact Working Range (Low)	1 mm [.039 in]



Contact Working Range (High)	1.6 mm[.063 in]
Point of Contact Area Plating Material	Gold
Contact Current Rating (Max)	.5 A

### Dimensions

Uncompressed Height	1.8 mm[.071 in]
---------------------	-----------------

### Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Packaging Features

Packaging Quantity	6000
Packaging Method	Tape & Reel

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1674954-1  
SHIELD FINGER 2026 WITH TAPE



TE Part # 1871059-1  
SHIELD FINGER 1715 ON TAPE (EM

## Documents

### Product Drawings

#### CAD Files

##### Customer View Model

[ENG\\_CVM\\_CVM\\_1857724-4\\_G.2d\\_dxf.zip](#)

English

#### 3D PDF

3D

##### Customer View Model

[ENG\\_CVM\\_CVM\\_1857724-4\\_G.3d\\_igs.zip](#)

English

##### Customer View Model

[ENG\\_CVM\\_CVM\\_1857724-4\\_G.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### Products for Mobile Equipment

English

#### Spring Fingers Quick Reference Guide

English

### Product Specifications

#### Product Specification

English

### Product Environmental Compliance

[MD\\_1857724-4\\_08052015148\\_dmtec](#)

English

[MD\\_1857724-4\\_08052015148\\_dmtec](#)

English