




TE Internal #: 1857925-1

Busbar Connector Contacts, Cable-to-Board, 4 Position, Wire & Cable, Size 8, Soldering, Copper Alloy, Silver, 50 A, Power, Board Mount

[View on TE.com >](#)

Connectors > Power Connectors > Power Busbar Connectors > Busbar Connector Contacts



Connector System: **Cable-to-Board**

Number of Positions: **4**

Connector & Contact Terminates To: **Wire & Cable**

Bus Bar Contact Size: **8**

Termination Method to Bus Bar: **Soldering**

Features

Product Type Features

| | |
|-----------------------------------|----------------|
| Product Type | Contact |
| Connector System | Cable-to-Board |
| Connector & Contact Terminates To | Wire & Cable |

Configuration Features

| | |
|-----------------------|----------|
| PCB Mount Orientation | Vertical |
| Number of Positions | 4 |

Electrical Characteristics

| | |
|----------------|-------|
| Current Rating | 50 A |
| Voltage Drop | 35 mV |

Contact Features

| | |
|----------------------------------|--------------|
| Contact Underplating Material | Nickel |
| Bus Bar Contact Size | 8 |
| Contact Base Material | Copper Alloy |
| Overall Contact Plating Material | Silver |
| Contact Current Rating (Max) | 50 A |

Termination Features

| | |
|-------------------------------|-----------|
| Termination Method to Bus Bar | Soldering |
|-------------------------------|-----------|

Mechanical Attachment

| | |
|--|--|
| | |
|--|--|



| | |
|-------------------------|-------------|
| Connector Mounting Type | Board Mount |
|-------------------------|-------------|

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 125 °C[-40 – 257 °F] |
|-----------------------------|----------------------------|

Operation/Application

| | |
|---------------------|-------|
| Circuit Application | Power |
|---------------------|-------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6648228-1
CROWN,SKT,#10



TE Part # 1410354-7
MULTI-GIG GUIDE PIN, 9MM 2.60

Documents

Product Drawings

[Busbar with contact pin size #8](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1857925-1_B.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1857925-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1857925-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English