



AMP Universal Power

TE Internal #: 175151-1

Power Contacts, Contact, 50 VAC / 300 VAC, Tin, 26 – 22 AWG  
Wire Size, .12 – .35 mm<sup>2</sup> Wire Size, Wire-to-Wire, Wire & Cable,  
Crimp, AMP Universal Power

[View on TE.com >](#)

Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**

Operating Voltage: **50 VAC, 300 VAC**

Contact Mating Area Plating Material: **Tin**

Wire Size: **.12 – .35 mm<sup>2</sup>**

**Features**

**Product Type Features**

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

**Electrical Characteristics**

Operating Voltage	50 VAC, 300 VAC
Insulation Resistance	1000

**Contact Features**

Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	12 A
Contact Type	Receptacle
Contact Retention Within Housing	With
Mating Tab Width	1.2 mm[.047 in]
Mating Tab Thickness	.64 mm[.025 in]
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material Thickness	.8 μm[31.49 μin]



Wire Contact Termination Area Plating Thickness	.8 µm[31.49 µin]
Wire Contact Termination Area Plating Material	Pre-Tin
Wire Contact Termination Area Plating Material Finish	Matte
Contact Orientation	Straight

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

### Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
Wire Insulation Support	With

### Dimensions

Wire Size	.12 – .35 mm <sup>2</sup>
Accepts Wire Insulation Diameter Range	1.2 – 2 mm[.047 – .079 in]

### Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Power
---------------------	-------

### Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

### Packaging Features

Packaging Method	Reel
Packaging Quantity	5000

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per

homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



TE Part # 176280-9  
UNIV POWER PLUG HSG 18P F/H



TE Part # 176275-1  
UNIV POWER PLUG HSG 8P F/H



TE Part # 176276-1  
AMP UNIVERSAL POWER PLUG 9P




TE Part # 176278-9  
UNIV POWER PLUG HSG 12P F/H




TE Part # 178481-1  
UP 3.96 4P PLUG HSG NATRL




TE Part # 178483-1  
UP 3.96 6P PLUG HSG NATRL




TE Part # 178482-1  
UP 3.96 5P PLUG HSG NATRL



TE Part # 178125-1  
U/POWER PLUG HSG 2P 7.92M/M




TE Part # 176273-1  
AMP UNIVERSAL POWR PLUG 4P






TE Part # 176272-1  
AMP UNIVERSAL POWER PLUG 3P







TE Part # 176270-1  
UNIV POWER PLUG HSG 1P F/H



TE Part # 292184-1  
HYBRID MINI DRAWER REC ASS'Y 6



## Also in the Series | AMP Universal Power



## Documents

### Product Drawings

AMP UNIVERSAL POWER REC CONT.

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_175151-1\\_T.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_175151-1\\_T.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_175151-1\\_T.3d\\_stp.zip](#)

English



### 3D PDF

English

#### Customer View Model

[ENG\\_CVM\\_175151-1\\_E.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_175151-1\\_E.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_175151-1\\_E.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Crimping of Universal Power Contact

English

#### Product Specification

Japanese

#### AMP Universal Power Connector

Japanese

### Product Environmental Compliance

[MD\\_175151-1\\_053120182142\\_dmtec](#)

English

[MD\\_175151-1\\_053120182142\\_dmtec](#)

English

### Instruction Sheets

#### Extraction Tool for UP(913923-1)

English

#### Instruction Sheet (non U.S.)

English

#### AMP UNIVERSAL POWER CONNECTOR SERIES

English

#### Instruction Sheet (non U.S.)

English

#### Hand Tool, PN 914181-1, Universal Power Contact (Was IS-505J)

Japanese

#### Instruction Sheet (non U.S.)

English