




Alcoswitch

TE Internal #: 1977263-3

Tactile Switches, Round Actuator Style, NO, Stainless Steel, Silver, Low Profile, 50 mA, 24 VDC, Single Pole - Single Throw Configuration (Pole-Throw)

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Tactile Switches



Actuator Style: **Round**

Operating Function: **NO**

Contact Base Material: **Stainless Steel**

Switch Contact Plating Material: **Silver**

Dust Proof: **No**

Features

Product Type Features

Product Type	Switch
Leg Style	Kinked
Illuminated	With
Actuator Style	Round
Dust Proof	No

Configuration Features

Tactile Feel	With
ESD Grounding Terminal	With
Ganged	With
Tactile	Yes
Snap Action	Without
Operating Function	NO
Support Bracket	Without
Configuration (Pole-Throw)	Single Pole - Single Throw



Number of Actuators	1
---------------------	---

Electrical Characteristics

Tactile Switch Voltage Rating	24 VDC
-------------------------------	--------

Body Features

Cover Material	Copper Alloy
----------------	--------------

Case Color	Ivory
------------	-------

Actuator Force	260 g[9.178 oz]
----------------	-----------------

Case Material	Nylon
---------------	-------

Bushing Style	Unthreaded
---------------	------------

Actuator Profile	Extended
------------------	----------

Actuator Material	Nylon
-------------------	-------

Actuator Color	Pink
----------------	------

Contact Features

Contact Base Material	Stainless Steel
-----------------------	-----------------

Switch Contact Plating Material	Silver
---------------------------------	--------

Tactile Switch Contact Current Rating	50 mA
---------------------------------------	-------

Termination Features

Termination Type	Printed Circuit Board
------------------	-----------------------

Mechanical Attachment

Tactile Switch Mounting Type	Surface Mount
------------------------------	---------------

Tactile Switch Mounting Angle	Vertical
-------------------------------	----------

Housing Features

Low Profile	With
-------------	------

Process Sealed	No
----------------	----

Dimensions

Actuator Length	.5 mm[.02 in]
-----------------	---------------

Button Width	2.3 mm[.118 in]
--------------	-----------------

	.122 in
--	---------

Usage Conditions

Temperature Rating	Standard °C
--------------------	-------------

Packaging Features



Packaging Method	Loose Piece
------------------	-------------

Other

Comment	(On) indicates momentary position.
---------	------------------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1825910-6
FSM4JH=6MM TACT SWITCH, HIGH TEMP



TE Part # 2-1825910-7
FSM14JH=6MM TACT SWITCH, HIGH TEMP



TE Part # 4-1437565-2
FSM4JSMATR=TACT SWITCH 6X6MIL



TE Part # 3-1437565-0
FSM2JSMATR=ON T/R



TE Part # 1977263-2 FSM1LPSTR=ESD GND SMD TACT SWITCH	TE Part # 2-1977223-8 FSM14JSMAS=6MM TACT SWITCH, SMT 160gf	TE Part # 1977263-1 FSM1LPS=ESD GND SMD TACT SWITCH	TE Part # 1977263-4 FSM1LPASTR=ESD GND SMD TACT SWITCH
--	--	--	---

Documents

Product Drawings

[FSM1LPAS=ESD GND SMD TACT SWITCH](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1977263-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1977263-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1977263-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English