



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Boots & Strain Relief

Protection & Strain Relief Accessory Type: **Strain Relief Kit**

Primary Product Material: **Glass-Filled Thermoplastic**

Primary Product Color: **Black**

Sealable: **No**

Operating Temperature Range: **-65 – 155 °C [ -85 – 311 °F ]**

## Features

### Product Type Features

Protection & Strain Relief Accessory Type	Strain Relief Kit
Sealable	No
Product Type	Accessory

### Body Features

Primary Product Material	Glass-Filled Thermoplastic
Primary Product Color	Black

### Usage Conditions

Operating Temperature Range	-65 – 155 °C[-85 – 311 °F]
-----------------------------	----------------------------

### Packaging Features

Packaging Method	Bag
Packaging Quantity	1

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2018 (181) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free


Solder Process Capability

Not applicable for solder process capability


## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Also in the Series | AMP GPR




Connector Contacts(2)



Power Contacts(9)



Rectangular Connector Seals(2)



Standard Rectangular Connectors(1)

## Documents

## Product Drawings

STRAIN RELIEF KIT,GPRB2

English

## Datasheets &amp; Catalog Pages

ARINC 600 Next Generation Receptacle Connector

English