




Relays, Contactors & Switches > Switches > Tactile Switches



Actuator Style: **Round**  
Operating Function: **NO**  
Contact Base Material: **Copper Alloy**  
Switch Contact Plating Material: **Silver**  
Dust Proof: **No**

Features

Product Type Features

|                |        |
|----------------|--------|
| Product Type   | Switch |
| Leg Style      | Kinked |
| Illuminated    | With   |
| Actuator Style | Round  |
| Dust Proof     | No     |

Configuration Features

|                            |                            |
|----------------------------|----------------------------|
| Tactile Feel               | With                       |
| ESD Grounding Terminal     | With                       |
| Ganged                     | With                       |
| Tactile                    | Yes                        |
| Snap Action                | Without                    |
| Operating Function         | NO                         |
| Support Bracket            | Without                    |
| Configuration (Pole-Throw) | Single Pole - Single Throw |



|                     |   |
|---------------------|---|
| Number of Actuators | 1 |
|---------------------|---|

Electrical Characteristics

|                               |        |
|-------------------------------|--------|
| Tactile Switch Voltage Rating | 24 VDC |
|-------------------------------|--------|

Body Features

|                   |                |
|-------------------|----------------|
| Cover Material    | Steel          |
| Case Color        | Black          |
| Actuator Force    | 100 g[3.53 oz] |
| Case Material     | Polyamide      |
| Bushing Style     | Unthreaded     |
| Actuator Profile  | Extended       |
| Actuator Material | PBT            |
| Actuator Color    | Brown          |

Contact Features

|                                       |              |
|---------------------------------------|--------------|
| Contact Base Material                 | Copper Alloy |
| Switch Contact Plating Material       | Silver       |
| Tactile Switch Contact Current Rating | 50 mA        |

Termination Features

|                  |                       |
|------------------|-----------------------|
| Termination Type | Printed Circuit Board |
|------------------|-----------------------|

Mechanical Attachment

|                               |              |
|-------------------------------|--------------|
| Tactile Switch Mounting Type  | Through Hole |
| Tactile Switch Mounting Angle | Vertical     |

Housing Features

|                |      |
|----------------|------|
| Low Profile    | With |
| Process Sealed | No   |

Dimensions

|                 |                 |
|-----------------|-----------------|
| Actuator Length | .7 mm[.028 in]  |
| Button Width    | 3.5 mm[.138 in] |
| Switch Height   | 4.3 mm[.169 in] |

Usage Conditions

|                    |         |
|--------------------|---------|
| Temperature Rating | High °C |
|--------------------|---------|

Packaging Features

|  |  |
|--|--|
|  |  |
|--|--|



|                  |                                    |
|------------------|------------------------------------|
| Packaging Method | Loose Piece                        |
| Other            |                                    |
| Comment          | (On) indicates momentary position. |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1825910-6  
FSM4JH=6MM TACT SWITCH, HIGH TEMP



TE Part # 2-1825910-7  
FSM14JH=6MM TACT SWITCH, HIGH TEMP



TE Part # 4-1437565-2  
FSM4JSMATR=TACT SWITCH 6X6MIL



TE Part # 3-1437565-0  
FSM2JSMATR=ON T/R



|                                                                                    |                                                                                     |                                                                                        |                                                                                     |
|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| <div></div> <div>TE Part # 1-1825955-0<br/>FSM5JH=6MM TACT SWITCH, HT W /ESD</div> | <div></div> <div>TE Part # 2-1825955-6<br/>FSM13JH=6MM TACT SWITCH, HT W /ESD</div> | <div></div> <div>TE Part # 2-1977223-8<br/>FSM14JSMAS=6MM TACT SWITCH, SMT 160gf</div> | <div></div> <div>TE Part # 3-1825955-1<br/>FSM15JAH=6MM TACT SWITCH, HT W/ESD</div> |
|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|

Documents

Product Drawings

FSM1JH=6MM TACT SWITCH, HT W/ESD

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1825955-2\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1825955-2\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1825955-2\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

TE Material Declaration

English