



Connectors > Automotive Connectors > Connector Housings



Connector & Housing Type: **Housing for Female Terminals**
Connector System: **Wire-to-Board, Wire-to-Device, Wire-to-Wire**
Number of Positions: **4**
Centerline (Pitch): **5 mm [.197 in]**
Sealable: **Yes**

Features

Product Type Features

Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Board, Wire-to-Device, Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	125 VAC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V, 80 V, 90 V, 125 V

Body Features

Cable Exit Angle	180°
Body Material	PBT GF
Primary Product Color	Gray
Connector Code	B



Contact Features

Contact Size	1.8mm
--------------	-------

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	Without
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	5 mm[.197 in]
--------------------	---------------

Dimensions

Product Width	30.6 mm[1.205 in]
Product Length	23.2 mm[.91 in]
Product Height	27.6 mm[1.09 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 184141-1 WIRE SEAL,RUBBER,SENSOR,PURPLE, LIM	 TE Part # 184140-1 WIRE SEAL,RUBBER,SENSOR, ORANGE	 TE Part # 184030-3 RECPT, CONTACT 070, PTPPHBZ	 TE Part # 184030-1 RECPT, CONTACT 070, AUPHBZ
 TE Part # 184355-2 2X2 CAP ASSEMBLY, B KEY, GRAY,	 TE Part # 184095-1 RECPT, CONTACT .070, AUPHBZ	 TE Part # 184095-2 RECPT, CONTACT .070, PTPPHBZ	 TE Part # 184139-1 WIRE SEAL,RUBBER,SENSOR,BLUE



TE Part # 184373-2 CONTACT, RECEPTACLE, .070 TYPE	TE Part # 184250-1 4P,2X2 PLUG ASSY W/O SLOT,KEYB	TE Part # 184252-1 2X2 PLG ASSY KEY B W/RET C4	TE Part # 184284-1 4P,2X2 PLUG ASSY W/O SLOT,KEYB
TE Part # 184299-1 2X2 PLG ASSY KEY D W/RET C4	TE Part # 184301-1 2X2 PLG ASSY KEY C C4	TE Part # 184307-1 2X2 CAP ASSY KEY D C4	TE Part # 184324-2 2X2 PLG ASSY KEY G C4 GRAY
TE Part # 184326-2 2X2 PLG ASSY KEY H C4 GRAY	TE Part # 184332-2 2X2 CAP ASSY KEY G C4 GRAY	TE Part # 184334-2 2X2 CAP ASSY KEY H C4 GRAY	TE Part # 2337311-1 2X2 PLG ASSY KEY H C3 W/CPA

Also in the Series | Sealed Sensor Connector SSC System

Automotive Connector Caps & Covers (7)	Automotive Connector Locks & Position Assurance(6)	Automotive Housings(174)	Automotive Seals & Cavity Plugs(3)
Automotive Terminals(8)	Insertion & Extraction Tools(1)	Other Automotive Connector Accessories(5)	

Documents



Product Drawings

2X2 PLUG ASSEMBLY, B KEY, GRAY

English

CAD Files

Customer View Model

ENG_CVM_184393-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_184393-2_E.3d_stp.zip

English

Customer View Model

ENG_CVM_184393-2_E.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English