



QSFP/QSFP+

TE Internal #: 1888631-1

QSFP, QSFP+ & zQSFP+, Cage Assembly, 1 x 1, Internal/External EMI Springs, Standard, Data Rate (Max) 14 Gb/s, 1 Port, Pin, QSFP /QSFP+

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > QSFP, QSFP+ & zQSFP+



Pluggable I/O Product Type: **Cage Assembly**
 Port Matrix Configuration: **1 x 1**
 EMI Containment Feature Type: **Internal/External EMI Springs**
 Thermal Accessory Type Included: **Heat Sink**
 Included Lightpipe: **No**

Features

Product Type Features

| | |
|-----------------------------------|-----------------------|
| Form Factor | QSFP+ |
| Cage Type | Single |
| Pluggable I/O Product Type | Cage Assembly |
| Thermal Accessory Type Included | Heat Sink |
| Connector System | Cable-to-Board |
| Sealable | No |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

| | |
|-------------------------------------|-------|
| Port Matrix Configuration | 1 x 1 |
| Number of Ports | 1 |
| Number of Rear EONs per Port Column | 2 |

Electrical Characteristics

| | |
|-----------------|---------|
| Data Rate (Max) | 14 Gb/s |
|-----------------|---------|

Body Features



| | |
|------------------------|-----------------|
| Heat Sink Finish | Anodized Black |
| Heat Sink Style | Pin |
| Heat Sink Height Class | PCI |
| Heat Sink Height | 4.2 mm[.165 in] |

Contact Features

| | |
|---|-----|
| PCB Contact Termination Area Plating Material | Tin |
|---|-----|

Termination Features

| | |
|---|--------------------------|
| Termination Post & Tail Length | 2.2 mm[.086 in] |
| Termination Method to Printed Circuit Board | Through Hole - Press-Fit |

Mechanical Attachment

| | |
|-------------------------|-------------|
| Connector Mounting Type | Board Mount |
|-------------------------|-------------|

Housing Features

| | |
|---------------|---------------|
| Cage Material | Nickel Silver |
|---------------|---------------|

Dimensions

| | |
|-----------------------------|------------------|
| PCB Thickness (Recommended) | 1.45 mm[.057 in] |
|-----------------------------|------------------|

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

| | |
|-------------------------------------|--|
| For Use With Pluggable I/O Products | QSFP Cable Assembly, QSFP MSA Compatible Transceiver |
| Pluggable I/O Applications | SFP+ Stacked Belly-to-Belly |
| Circuit Application | Signal |

Industry Standards

| | |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

| | |
|------------------|------------|
| Packaging Method | Box & Tray |
|------------------|------------|

Other

| | |
|------------------------------|-------------------------------|
| EMI Containment Feature Type | Internal/External EMI Springs |
| Included Lightpipe | No |
| Enhancements | Standard |



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | | | |
|---|---|---|--|
|  <p>TE Part # CAT-C11-H50114 QSFP to QSFP I/O Cable Assembly: 30 AWG</p> |  <p>TE Part # CAT-C11-H50111 QSFP-Four SFP+ I/O Cable Assembly 30 AWG</p> |  <p>TE Part # 1761987-9 ReceptacleConnAssm38PosTape/Re</p> |  <p>TE Part # 2110819-1 QSFP+ Enh EVERCLEAR PT Conn</p> |
|---|---|---|--|




TE Part # 1888810-2
EMI/Dust Cover,XFP And QSFP



TE Part # CAT-C11-H5011
QSFP-Four SFP+ I/O Cable Assembly
28 AWG



TE Part # CAT-C11-H5011142
QSFP to QSFP I/O Cable Assembly: 33
AWG



TE Part # 2053638-5
C/A, QSFP, 5M, P1-P2, UNEQUALIZED



TE Part # 1-2220639-0
QSFP TO QSFP, ACTIVE, 28AWG, 10M



TE Part # 1-2220639-3
QSFP TO QSFP, ACTIVE, 28AWG, 13M



TE Part # 2053638-4
C/A, QSFP, 4M, P1-P2, UNEQUALIZED




TE Part # 2185265-1
ASSY, SEATING TOOL KIT



TE Part # 2202165-4
QSFP TO QSFP, 26AWG, FDR, 4.0
METER



TE Part # 2202165-5
QSFP TO QSFP, 26AWG, FDR, 5.0
METER



TE Part # 2366192-1
ASSY SEATING TOOL, 1X1



TE Part # 2829040-2
QSFP IB EDR, 33AWG, 1.0M



TE Part # 2829040-4
QSFP IB EDR, 30AWG, 1.0M



TE Part # 2829040-6
QSFP IB EDR, 30AWG, 2.0M



TE Part # 2829040-7
QSFP IB EDR, 26AWG, 2.0M



TE Part # 2829040-8
QSFP IB EDR, 26AWG, 3.0M

Also in the Series | **QSFP/QSFP+**



Heat Sinks(1)



Pluggable I/O Cable Assemblies(33)



QSFP, QSFP+ & zQSFP+(168)

Documents



Product Drawings

Cage Assy PCI Hsink QSFP Thru

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1888631-1_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1888631-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1888631-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1773408-1 Pluggable Input/Output Solutions catalog - QSFP section

English

4-1773455-5 - Quick Reference Guide QSFP/QSFP+ Solutions

English

Quad Small Form-factor Pluggable (QSFP) Products Datasheet 6-1773447-7

English

Product Specifications

Application Specification

English

Product Environmental Compliance

[MD_1888631-1_012920181251_dmtec](#)

English

[MD_1888631-1_012920181251_dmtec](#)

English