

1969657-1 ✓ ACTIVE

FASTON | FASTON 250

TE Internal #: 1969657-1

Crimp Terminal Housings, Receptacle, Receptacle, 1 Position, Flag,
UL 94V-0, Black, Nylon, Mating Alignment, Cable Mount (Free-
Hanging), FASTON 250

[View on TE.com >](#)



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**

Housing Type: **Receptacle**

Number of Positions: **1**

Terminal Orientation: **Flag**

UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Product Type	Terminal Housing
Sealable	No
Housing Type	Receptacle
Insulated	No

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Flag
Contact Mating Retention	Without

Mechanical Attachment



Mating Alignment	With
Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
------------------	-------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-P851-T1
PCB Power Relay: 30 amp, Monostable DC



TE Part # 2238171-3
250 FASTON,FLAG,REC.,22-12 AWG, TPBR



TE Part # 1-1558676-9
T9GS1L24-110WG



TE Part # 1-1558676-3
T9GS1L24-12WG



TE Part # 1-1558676-4
T9GS1L24-15WG



TE Part # 1-1558676-5
T9GS1L24-18WG



TE Part # 1-1558676-6
T9GS1L24-22WG



TE Part # 1-1558676-7
T9GS1L24-24WG



TE Part # 1-1558676-8
T9GS1L24-48WG



TE Part # 1-1558676-1
T9GS1L24-5WG



TE Part # 1-1558676-2
T9GS1L24-9WG



TE Part # 1-1558677-9
T9GS2L24-110WG



TE Part # 1-1558677-3
T9GS2L24-12WG



TE Part # 1-1558677-4
T9GS2L24-15WG



TE Part # 1-1558677-5
T9GS2L24-18WG



TE Part # 1-1558677-6
T9GS2L24-22WG



TE Part # 1-1558677-7
T9GS2L24-24WG



TE Part # 1-1558677-8
T9GS2L24-48WG



TE Part # 1-1558677-1
T9GS2L24-5WG



TE Part # 1-1558677-2
T9GS2L24-9WG

Also in the Series | **FASTON 250**



Compression Connectors(4)



Crimp Terminal Housings(143)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(144)



Quick Disconnects(455)



Splices(4)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1969657-1_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1969657-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1969657-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PB 30A PCB Relay T9G Series

English

Introductory Flyer - High Temperature FASTON Housings

English

Product Environmental Compliance

TE Material Declaration

English