




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **7**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Header Type	Partially Shrouded
Rectangular Power Connector Type	Header
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stacking Configuration	End to End
Number of Positions	7
PCB Mount Orientation	Vertical
Number of Power Positions	7
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------



Body Features

Connector Profile	Low
-------------------	-----

Contact Features

Contact Layout	Inline
Contact Base Material	Brass
Contact Current Rating (Max)	8 A
Contact Retention Within Housing	Without
Contact Type	Pin
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	1 µm[39.37 µin]
Contact Termination Area Plating Thickness	.8 µm[31.49 – 70.86 µin]

Termination Features

Termination Post & Tail Length	3.7 mm[.146 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment	With
PCB Mount Alignment	Without
PCB Mount Retention	Without
Connector Mounting Type	Board Mount
Mating Retention	With
Mating Retention Type	Latch

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
Housing Color	Natural
Housing Material	PBT GF

Dimensions

PCB Thickness (Recommended)	.06 mm[1.6 in]
Width	10.7 mm[.421 in]
Mating Post Length	7.7 mm[.3 in]
Height	8.2 mm[.32 in]
Length	27.66 mm[1.089 in]



Usage Conditions

Operating Temperature Range	-25 – 105 °C[-13 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Method	Bag
Packaging Quantity	650

Other

For Use With	Plug Housing
--------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>










EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 1-1123722-7 3.96 EP PLUG HSG 7P(NATURAL)	 TE Part # 1123721-2 ECONOMY POWER CONN REC CONT	 TE Part # 2110989-1 EP 2.5 RCPT CONTACT, 26-22 AWG	 TE Part # 7-1123724-1 3.96EP HDR ASSY 4(7)P (NATURAL GWT)
 TE Part # 1744416-7 7 POS EP II HSG, GLOW WIRE	 TE Part # 1744544-7 EP II TPA 07P, BLACK	 TE Part # 1123721-1 EP CONN. REC CONTACT	 TE Part # 1-2316952-6 3.96 EP HDR ASSY 6P,NO PIN 2,4
 TE Part # 1744107-2 3.96 EPHDR ASSY 7P OMIT #3 PIN	 TE Part # 2-2316952-0 3.96 EP HDR ASSY 10P, NO PIN 3,5,7,9	 TE Part # 2316952-4 3.96 EP HDR ASSY 4P, NO PIN 2,3	 TE Part # 2316952-6 3.96 EP HDR ASSY 6P,NO PIN 2,3,5
 TE Part # 2316952-7 3.96 EP HDR ASSY 7P, NO PIN 1,3,5	 TE Part # 3-2316952-0 3.96 EP HDR ASSY 10P, NO PIN 7,9		

Also in the Series | Economy Power



Connector Contacts(1)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(166)

PCB Latches, Locks & Retainers(2)

Power Contacts(8)

Rectangular Connector Housings(1)

Rectangular Power Connectors(301)

Wire-to-Board Connector Assemblies & Housings(141)

Wire-to-Board Connector Contacts(6)

Documents

Product Drawings
3.96 EP HDR ASSY 7P(NATURAL)

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1123723-7_AD_c-1-1123723-7-ad.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1123723-7_AD_c-1-1123723-7-ad.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1123723-7_AD_c-1-1123723-7-ad.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages
1-1773885-9 Economy Power Connectors
English

Product Specifications
Application Specification
English
Application Specification
Japanese
Application Specification
English

Product Environmental Compliance
MD_1-1123723-7_08072018522_dmtec
English
MD_1-1123723-7_08072018522_dmtec
English

Instruction Sheets
Instruction Sheet (non U.S.)
Japanese
Economy Power (EP) Connector
Japanese