



Connectors > RF Coax Connectors > RF Adapters > In-Series Adapters



RF Interface: **BNC**

RF Connector Center Contact Material: **Brass**

RF Connector Center Contact Plating Material: **Gold**

Impedance: **50 Ω**

Connector System: **Cable-to-Cable**

Features

Product Type Features

Grounding Options	None
RF Interface	BNC
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Plating Material	Nickel
Body Material	Brass

Contact Features

RF Connector Center Contact Material	Brass
RF Connector Center Contact Plating Material	Gold

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	18.6 mm[.73 in]
--------------------	-----------------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 85 °C[-85 – 185 °F]

Operation/Application

Operating Frequency	4 GHz
Circuit Application	Power & Signal

Packaging Features

Packaging Quantity	50
Packaging Method	Tray

Other

Gasket Material	Silicone Rubber
Grade	Professional

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: DEC 2014 (161) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | Alcoswitch ADP



Card Edge Connector Housings(4)



DIP & SIP Switches(8)



RJ45 Connectors(1)

Documents

Product Drawings

[BNC R/A Y Adp 50Ohm Nickel Pltd](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-1337461-0_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1337461-0_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1337461-0_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.