



[Alcoswitch](#) | [Alcoswitch TSP](#)

TE Internal #: 1-1571990-7

Push Button Switches, Single Pole - Double Throw Configuration (Pole-Throw), Switch, Single Actuator, Extended Actuator Profile, Alcoswitch TSP

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Push Button Switches



Configuration (Pole-Throw): **Single Pole - Double Throw**

Push Button Switch Product Type: **Switch**

Number of Actuators: **Single**

Actuator Profile: **Extended**

Bushing Style: **Unthreaded**

Features

Product Type Features

Switch Type	Pushbutton
Dust Proof	No
Push Button Switch Product Type	Switch
Illuminated	No
Actuator Style	Round

Configuration Features

ESD Grounding Terminal	Without
Ganged	No
Configuration (Pole-Throw)	Single Pole - Double Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Tactile	No
Operating Function	On (On)

Electrical Characteristics

Push Button Switch Voltage Rating	20 VDC
-----------------------------------	--------

Body Features

Case Material	Thermoplastic (LCP)
---------------	---------------------



Actuator Material	Thermoplastic
Actuator Profile	Extended
Bushing Style	Unthreaded
Actuator Color	Black

Contact Features

Contact Base Material	Copper Alloy
Push Button Switch Contact Current Rating	.4 A
Switch Contact Plating Material	Gold over Nickel

Termination Features

Termination Type	Printed Circuit
------------------	-----------------

Mechanical Attachment

Mounting Angle	Right Angle
Push Button Switch Mounting Type	Through Hole

Housing Features

Low Profile	No
Process Sealed	Yes

Dimensions

Actuator Length	5.08 mm[.2 in]
Button Width	2.54 mm[.1 in]

Usage Conditions

Temperature Rating	High
--------------------	------

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Other

Comment	(On) indicates momentary position.
---------	------------------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JUNE 2022
(224)

Candidate List Declared Against: JUN 2016
(169)

SVHC > Threshold:
Not Yet Reviewed

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts



TE Part # 1571990-1
TSPD11CGPC004



TE Part # 1-1437573-5
TSPD11CGRA0=60377, 40287



TE Part # 1437573-7
TSP71190=TSPD11CGRA0 W/SPECIAL



TE Part # 1571990-4
TSPD11CGRA004



TE Part # 2-1571990-1
TSPD11FGVRA004



TE Part # 2-1571990-2
TSPDF11CGPC004



TE Part # 2-1571990-5
TSPDF11CGRA004



TE Part # 2-1571990-7
TSPDF11CGVRA004



TE Part # 2-1571990-8
TSPDF11FGPC004



TE Part # 2-1571990-9
TSPDF11FGRA004



TE Part # 1-1437573-1
TSPD11CGPC0=PB 60377, 40287



TE Part # 1-1437573-3
TSPD11CGPC2=60377, 40287



TE Part # 1-1437573-4
TSPD11CGPCV0=60377, 40287



TE Part # 1-1437573-7
TSPD11CGRA2=VIKING PUSH
BUTTON



TE Part # 1-1437573-9
TSPD11CGSRA0=60377, 40287



TE Part # 2-1437573-0
TSPD11CGSRA2=VIKING PUSH
BUTTO



TE Part # 2-1437573-2
TSPD11CGVRA0=60377, 40287



TE Part # 2-1437573-3
TSPD11CGWW0=60377, 40287



TE Part # 2-1437573-4
TSPD11FGPC0=60377, 40287



TE Part # 2-1437573-5
TSPD11FGPCV0=60377, 40287

Also in the Series | Alcoswitch TSP



Card Ejectors(1)



Push Button Switches(29)

Documents

Product Drawings

TSPD11FGRA004

English

CAD Files

3D PDF

English

Customer View Model



[ENG_CVM_1-1571990-7_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_1-1571990-7_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-1571990-7_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English