

1991253-9 ✓ ACTIVE

AMPLIMITE


TE Internal #: 1991253-9

D-Sub Backshells & Clamps, Backshell, Clam Shell, 9 Position, Size 1, Cable Exit Angle 180° (In-Line), Wire & Cable

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Backshell**

Cable Clamp Type: **Clam Shell**

Number of Positions: **9**

Compatible With Connector Shell Size: **1**

Shielded: **No**

Features

Product Type Features

Clam Shell Length	Standard
Grommets	Without
Slide Latch	Without
D-Shaped Connector Accessories	Backshell
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	9
---------------------	---

Body Features

Shield Plating Material	None
Cable Clamp Material	Carbon Steel
Color	Black
Backshell Material	Polyamide
Cable Clamp Type	Clam Shell
Cable Exit Angle	180° (In-Line)

Mechanical Attachment

Screw & Hole Thread Size	14702
--------------------------	-------

Dimensions

Cable Insulation Diameter Range	3 – 11 mm [.118 – .433 in]
---------------------------------	----------------------------

Operation/Application

Compatible With Connector Shell Size	1
Shielded	No

Industry Standards

Cover Flammability Rating	UL 94V-2
---------------------------	----------

Packaging Features

Packaging Quantity	100
Packaging Method	Bag, Loose Piece

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-747905-2
9 Rcpt Solder Cup, Gold Flash,

Documents

Product Drawings

[9 WAY LOW COST D SUB BACKSHELL](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1991253-9_A_c-1991253-9-a.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1991253-9_A_c-1991253-9-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1991253-9_A_c-1991253-9-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.