

1-1609112-8 ✓ ACTIVE

Corcom | Corcom CU

TE Internal #: 1-1609112-8

IEC Unfiltered Inlets, 15 A, IEC 60320/C-14, Male Receptacle, 3/16"

Faston Output, 250 VAC, Corcom CU

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > IEC Unfiltered Inlets > IEC Unfiltered Inlets, Corcom CU Series



Filter Current Rating: 15 A

Input Connector Type: IEC 60320/C-14

Input Connector Style: Male Receptacle

Filter Output Termination Type: 3/16" Faston

Voltage Rating (Max): 250 VAC

[All IEC Unfiltered Inlets, Corcom CU Series \(4\)](#)

Features

Product Type Features

Input Connector Type	IEC 60320/C-14
Input Connector Style	Male Receptacle
Filter Output Termination Type	3/16" Faston

Electrical Characteristics

Filter Current Rating	15 A
Voltage Rating (Max)	250 VAC

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Corcom CU



Documents

Product Drawings
15CU15S1=F8314



English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-1609112-8_B1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1609112-8_B1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1609112-8_B1.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

[1654001_Corcom_Product_Guide_CU_Series](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English

[CORCOM_CU_SERIES](#)

English

Agency Approvals

[APPLIANCE INLET, CU SERIES, CB TEST CERTIFICATE](#)

English