

1-1609112-9 ✓ ACTIVE

Corcom | Corcom CU

TE Internal #: 1-1609112-9

Multi-Function Inlet Filters, Power Entry Module, None Input, SPST, None, Vertical, 15 A, Snap-In, IEC Input, .187" FASTON Output, 250 VAC, Corcom CU

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > CORCOM CU SERIES MULTI-FUNCTION INLET FI



Filter Type: **Power Entry Module**

Input Voltage Selection: **None**

Filter Switch Type: **SPST**

Filter Shield Type: **None**

Mount Angle: **Vertical**

[All CORCOM CU SERIES MULTI-FUNCTION INLET FI \(19\)](#)

Features

Product Type Features

Ground Choke Option	No
Level Of Filtering	None
Filter Type	Power Entry Module
Filter Switch Type	SPST
Filter Input Termination Type	IEC
Filter Output Termination Type	.187" FASTON
Filtering Requirements	Unfiltered
Filter Connector Type	IEC 60320-1 C-14

Configuration Features

Fuse Options	None
--------------	------

Electrical Characteristics

Input Voltage Selection	None
Leakage Current (Max) (120VAC, 60Hz)	2 μ A
Leakage Current (Max) (250VAC, 50Hz)	5 μ A
Filter Current Rating	15 A
Voltage Rating (Max)	250 VAC

Body Features



Filter Shield Type	None
--------------------	------

Mechanical Attachment

Mount Angle	Vertical
Filter Mount Style	Snap-In

Housing Features

Low Profile	Yes
-------------	-----

Dimensions

Panel Thickness Range	.8 – 2.5 mm [.031 – .098 in]
-----------------------	------------------------------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Operation/Application

For Use With	14 AWG Power Cord
--------------	-------------------

Other

Comment	15A versions tested by Underwriters Laboratories to US and Canadian requirements and are VDE approved to 10A @ 250 VAC.
---------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Corcom CU



Documents

Product Drawings

[15CU15BS1=F8315](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-1609112-9_B1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1609112-9_B1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1609112-9_B1.2d_dxf.zip](#)

English

[3D PDF](#)



3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

[1654001_Corcom_Product_Guide_CU_Series](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English

[CORCOM_CU_SERIES](#)

English

Agency Approvals

[APPLIANCE INLET, CU SERIES, CB TEST CERTIFICATE](#)

English