



CII

TE Internal #: 1-1617754-8


Mid-Range Relays, 4 Form C, 4PDT, 4 C/O, Coil Suppression

Diode, Tin-Lead Terminal Plating, 10 A, 28 VDC Coil Voltage, 290 Ω

Coil Resistance

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Mil-Aero Relays > Mid-Range Relays



Mid-Range Relay Contact Arrangement: **4 Form C, 4PDT, 4 C/O**

Coil Suppression Diode: **With**

Auxiliary Contacts: **Without**

Terminal Plating: **Tin-Lead**

Mid-Range Relay Contact Current Rating: **10 A**

**Features**

**Product Type Features**

Enclosure Type	Hermetically Sealed
Terminal Configuration	Solder Hook
Product Type	Relay
Relay Type	Military/Aerospace Mid-Range

**Electrical Characteristics**

Vibration	30G's, 10 – 3000Hz
Shock	200G's, 6ms
Coil Suppression Diode	With
Mid-Range Relay Coil Voltage Rating	28 VDC
Mid-Range Relay Coil Resistance	290 Ω
Back EMF Suppression	With
Coil Magnetic System	Polarized, Monostable
Actuating System	DC

**Contact Features**

Mid-Range Relay Contact Arrangement	4 Form C, 4PDT, 4 C/O
Auxiliary Contacts	Without
Terminal Plating	Tin-Lead
Mid-Range Relay Contact Current Rating	10 A



Contact Base Material	Silver Cadmium Oxide
-----------------------	----------------------

### Mechanical Attachment

Mid-Range Relay Mounting Type	Raised Vertical Flange Mount
-------------------------------	------------------------------

### Usage Conditions

Operating Temperature Range	-70 – 125 °C
-----------------------------	--------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------

EU ELV Directive 2000/53/EC	Not Compliant
-----------------------------	---------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not lead free process capable
---------------------------	-------------------------------

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




TE Part # 4-1617004-8  
B07D934BC2-0052 = M5757/23-004



TE Part # 2-1617582-0  
A07B335BC1=RELAY




TE Part # 1-1617004-2  
B07D034BZ2-0357 = M5757/23-041




TE Part # 1-1617749-3  
FCA-210-1019M=M83536/10-019M




TE Part # 4-1617002-1  
B07B035BC1 = B07 10 AMP RELAY



TE Part # 9-1617748-9  
FCA-210-0924L=M83536/9-024L




TE Part # 1617788-4  
FCA-210-0914M=M83536/9-014M




TE Part # 1617752-9  
FCA-210-CY8




TE Part # 1617005-9  
B07D992BZ2-0050 = M5757/23-002




TE Part # 1-1617749-8  
FCA-210-1022M=M83536/10-022M




TE Part # 2-1617749-1  
FCA-210-1024L=M83536/10-024L



TE Part # 1-1617784-0  
FCA-210-1003M=M83536/10-003M




TE Part # 1-1617784-8  
FCA-210-1008L=M83536/10-008L




TE Part # 1-1617788-6  
FCA-210-0926L=M83536/9-026L




TE Part # 1617002-6  
B07A112BB1 = RELAY.




TE Part # 2-1617784-7  
FCA-210-1013M=M83536/10-013M




TE Part # 2-1617788-5  
FCA-210-0933M=M83536/9-033M



TE Part # 3-1617784-2  
FCA-210-1016L=M83536/10-016L



TE Part # 3-1617788-1  
FCA-210-0936M=M83536/9-036M



TE Part # 4-1617784-0  
FCA-210-1021L=M83536/10-021L

Documents

Product Drawings

FCA-410-1621L=M83536/16-021L

FCA-410-1621L

Mid-Range Relays, 4 Form C, 4PDT, 4 C/O, Coil Suppression Diode, Tin-Lead  
Terminal Plating, 10 A, 28 VDC Coil Voltage, 290  $\Omega$  Coil Resistance



English

---

**Datasheets & Catalog Pages**

[5-1773450-5\\_sec5\\_FCA-410](#)

English