



CII

TE Internal #: 1-1423156-3

Signal Relays, 120 VAC Contact Voltage, Socket, Plug-In, 24 VAC Coil Voltage, 10 A, 4 Form C (4PDT), 120 VAC Switching Voltage, Monostable, AC, 4 Pole

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Signal Relays



Contact Voltage Rating: **120 VAC**

Signal Relay Mounting Type: **Socket**

Signal Relay Terminal Type: **Plug-In**

Signal Relay Coil Voltage Rating: **24 VAC**

Signal Relay Contact Current Rating: **10 A**

Features

Product Type Features

Product Type	Relay
--------------	-------

Electrical Characteristics

Coil Power Rating (AC)	6 VA
Actuating System	AC
Coil Type	Monostable
Coil Special Features	LED
Contact Voltage Rating	120 VAC
Signal Relay Coil Voltage Rating	24 VAC
Signal Relay Contact Switching Voltage (Max)	120 VAC
Signal Relay Coil Magnetic System	Monostable, AC

Contact Features

Signal Relay Terminal Type	Plug-In
Signal Relay Contact Current Rating	10 A
Signal Relay Contact Arrangement	4 Form C (4PDT)
Contact Number of Poles	4

Mechanical Attachment

Signal Relay Mounting Type	Socket
----------------------------	--------



Packaging Features

Packaging Method	Box & Carton
------------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1423155-4
GPCN=RELAY, 48VDC W/BLOWOUT
DE



Documents

Product Drawings

GPGQ=RLY,24VAC,Q OPT

English

Datasheets & Catalog Pages

5-1773450-5_sec12_GP_ML_TR

English