


AMP SMA

TE Internal #: 1-1478916-0
RF Connectors, SMA RF Interface, Plug, 50 Ω, KX 22A / KX 3B,
Threaded, 26 GHz Operating Frequency, Cable-to-Cable, 1
Position, Sealable, AMP SMA

[View on TE.com >](#)



Connectors > RF Coax Connectors > RF Connectors



RF Interface: **SMA**
RF Connector Style: **Plug**
RF Connector Mated Outer Diameter (Approximate): **6.35 mm [.25 in]**
Impedance: **50 Ω**
Compatible With RF Cable Type: **KX 22A, KX 3B**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector Seal Type	Gasket
RF Interface	SMA
RF Connector Style	Plug
Compatible With RF Cable Type	KX 22A, KX 3B
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features



Cable Connector Orientation	Straight
Body Material	Stainless Steel
Body Material Finish	Plated
Body Plating Material	Gold

Contact Features

RF Connector Center Contact Underplating Material	Copper
RF Connector Contact Configuration	Not Captivated
Ferrule Plating Material	Gold
Crimp Type	Hex
Ferrule Material	Brass
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

RF Connector Coupling Mechanism	Threaded
RF Contact Captivation Method	Mechanical
Detent	Without

Dimensions

Product Length	15.05 mm[.593 in]
RF Connector Mated Outer Diameter (Approximate)	6.35 mm[.25 in]

Usage Conditions

Operating Temperature Range	-65 – 165 °C[-85 – 329 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency	26 GHz
---------------------	--------

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Other

Coupling Nut Plating Material	Gold
Gasket Material	Silicone Rubber



Coupling Nut Base Material	Stainless Steel
Grade	Professional
Dielectric Material	PTFE

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (3.15% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 1-1478963-0 SMA PNL SKT RCPT, 2/FLNG GSS	 TE Part # 1-1478979-0 SMA STR PCB SKT GSS	 TE Part # 1-1478966-0 SMA B/HD SKT RCPT GSS	 TE Part # 1-1478968-0 SMA PNL SKT LNCH STUB 4/FLNG GSS NCC
 TE Part # 1-1478988-0 SMA B/HD JK DS RG405 GSS	 TE Part # 9-1478248-0 PRO-C HEX DIE RG174-RG178	 TE Part # 1-1478978-0 SMA R/A PCB SKT GSS	 TE Part # 2-1478966-0 SMA B/HD SKT RCPT PSS
 TE Part # 2-1478968-0 SMA PNL SKT LNCH STUB 4/FLNG PSS NCC			

Also in the Series

AMP SMA

 Battery Holders(1)	 Between Series Adapters(1)	 Coax Terminators(1)	 In-Series Adapters(11)
 Rack & Panel Ferrules & Inserts(1)	 RF Cable Assemblies(2)	 RF Connector Hardware(2)	 RF Connector Launchers(8)



RF Connector Shrouds(3)



RF Connectors(297)

Documents

Product Drawings

SMA STR PLG C/CRMP RG174 GSS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1478916-0_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1478916-0_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1478916-0_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773725-8_RF_COAX_QRG

English

Product Specifications

Product Specification

English