



Industrial RJ45 Variant 3

TE Internal #: 1-1546406-1

Modular Jack & Plug Caps & Covers, Closure Cap, RJ45, Wire & Cable, Industrial RJ45 Variant 3

[View on TE.com >](#)

Connectors > Modular Jacks & Plugs > Modular Jack & Plug Accessories > Modular Jack & Plug Caps & Covers



Modular Jacks & Plugs Accessory Type: **Closure Cap**

Modular Jack & Plug Interface Type: **RJ45**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

| | |
|--|--------------|
| Connectors & Connector Components Type | Accessory |
| Closure Cap Type | Receptacle |
| Modular Jacks & Plugs Accessory Type | Closure Cap |
| Modular Jack & Plug Interface Type | RJ45 |
| Connector & Contact Terminates To | Wire & Cable |

Body Features

| | |
|--------------|--------|
| Cap Color | Black |
| Cap Material | Delrin |
| Cover Color | Black |

Housing Features

| | |
|---------------------------------|----------|
| Compatible With Connector Shape | Circular |
| Housing Color | Black |

Packaging Features

| | |
|--------------------|---------|
| Packaging Quantity | 1 |
| Packaging Method | Package |

Other

| | |
|----------------|------------------|
| Lanyard | With |
| Lanyard Length | 92.2 mm[3.63 in] |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | | | |
|---|---|--|--|
|  <p>TE Part # 1-1546405-1 ETHERNET DIRECT PCB MNT RCPT</p> |  <p>TE Part # 1546414-4 ETHRNT RJ-45 BLKHD PASSTHRU12"</p> |  <p>TE Part # 1546413-3 ETHERNET RJ-45 BLKHD PASSTHRU</p> |  <p>TE Part # 1-1546409-1 ETHERNET RECEPTACL W/PC BOARD</p> |
|---|---|--|--|



Also in the Series | **Industrial RJ45 Variant 3**



Documents

Product Drawings

ETHERNET CLOSURE CAP RECPT W/LANYRD

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1546406-1_C.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1546406-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1546406-1_C.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

INDUSTRIAL_ETHERNET_PRODUCTS

English