

1004X ✓ ACTIVE

Kilovac | Kilovac 1000 Series

TE Internal #: 1-1618059-6

Protective Relays, 1 Form A, SPST-NO, 1 NO, 10 A, 460 VAC Input,  
Flanged, Three Phase, Kilovac 1000 Series

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Protective Relays



Protective Relay Contact Arrangement: **1 Form A, SPST-NO, 1 NO**

Protective Relay Contact Current Rating: **10 A**

Protective Relay Input Voltage: **460 VAC**

Time Delay: **Without**

Protective Relay Mounting Type: **Flanged**

## Features

### Product Type Features

Relay Type	Protective Relay
Product Type	Relay
Protection Function	Phase Failure, Voltage Sensitive
Time Delay	Without
Phase	Three

### Electrical Characteristics

Actuating System	AC
Protective Relay Input Voltage	460 VAC

### Contact Features

Contact Arrangement (Additional Output)	None
Protective Relay Contact Arrangement	1 Form A, SPST-NO, 1 NO
Protective Relay Contact Current Rating	10 A

### Mechanical Attachment

Protective Relay Mounting Type	Flanged
--------------------------------	---------

### Usage Conditions

Operating Temperature Range	-40 – 70 °C
-----------------------------	-------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

### Compatible Parts



### Also in the Series | Kilovac 1000 Series



Protective Relays(6)

## Documents

### Product Drawings

[1004X=WILMAR PHASE FAILURE RE](#)

English

---

### Datasheets & Catalog Pages

[5-1773450-5\\_sec11\\_1000](#)

English