



MICTOR

TE Internal #: 1-1658012-2

PCB Mount Receptacle, Vertical, Board-to-Board, 56 Position, .8 mm [.031 in] Centerline, Fully Shrouded, Gold, Surface Mount, Power & Signal, Black

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **56**

Centerline (Pitch): **.8 mm [.031 in]**

Features

Product Type Features

| | |
|-----------------------------------|-----------------------|
| PCB Connector Assembly Type | PCB Mount Receptacle |
| Connector System | Board-to-Board |
| Header Type | Fully Shrouded |
| Sealable | No |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

| | |
|----------------------------------|-------------------|
| Stackable | No |
| Connector Contact Load Condition | Differential Load |
| PCB Mount Orientation | Vertical |
| Number of Positions | 56 |
| Board-to-Board Configuration | Parallel |

Electrical Characteristics

| | |
|---------------------------------------|---------|
| Dielectric Withstanding Voltage (Max) | 675 VAC |
| Insulation Resistance | 2 MΩ |



| | |
|-----------|-------|
| Impedance | 100 Ω |
|-----------|-------|

| | |
|-------------------|---------|
| Operating Voltage | 125 VAC |
|-------------------|---------|

Body Features

| | |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|

Contact Features

| | |
|---|--------------------|
| PCB Contact Termination Area Plating Material Thickness | .25 μm[9.8425 μin] |
|---|--------------------|

| | |
|------------------|-----------------|
| Mating Tab Width | .38 mm[.015 in] |
|------------------|-----------------|

| | |
|----------------------|----------------|
| Mating Tab Thickness | .2 mm[.008 in] |
|----------------------|----------------|

| | |
|----------------------|-------------|
| Contact Shape & Form | Single Beam |
|----------------------|-------------|

| | |
|---|------|
| PCB Contact Termination Area Plating Material | Gold |
|---|------|

| | |
|-----------------------|-----------------|
| Contact Base Material | Phosphor Bronze |
|-----------------------|-----------------|

| | |
|--------------------------------------|------|
| Contact Mating Area Plating Material | Gold |
|--------------------------------------|------|

| | |
|--|--------------------|
| Contact Mating Area Plating Material Thickness | .25 μm[9.8425 μin] |
|--|--------------------|

| | |
|--------------|--------|
| Contact Type | Socket |
|--------------|--------|

| | |
|------------------------------|---------------|
| Contact Current Rating (Max) | 1.25 A, 9.5 A |
|------------------------------|---------------|

Termination Features

| | |
|---|-----------------|
| Rectangular Termination Post & Tail Thickness | .15 mm[.006 in] |
|---|-----------------|

| | |
|---|-----------------|
| Rectangular Termination Post & Tail Width | 1.77 mm[.07 in] |
|---|-----------------|

| | |
|---|---------------|
| Termination Method to Printed Circuit Board | Surface Mount |
|---|---------------|

Mechanical Attachment

| | |
|--------------------------|----------------|
| PCB Mount Alignment Type | Locating Posts |
|--------------------------|----------------|

| | |
|------------------|------|
| Mating Retention | With |
|------------------|------|

| | |
|------------------|---------|
| Mating Alignment | Without |
|------------------|---------|

| | |
|---------------------|------|
| PCB Mount Retention | With |
|---------------------|------|

| | |
|---------------------|------|
| PCB Mount Alignment | With |
|---------------------|------|

| | |
|-------------------------|-------------|
| Connector Mounting Type | Board Mount |
|-------------------------|-------------|

Housing Features

| | |
|--------------------|----------------|
| Centerline (Pitch) | .8 mm[.031 in] |
|--------------------|----------------|

| | |
|------------------|------------------------------|
| Housing Material | LCP (Liquid Crystal Polymer) |
|------------------|------------------------------|

Dimensions

| | |
|------------------|-----------------|
| Connector Height | 3.05 mm[.12 in] |
|------------------|-----------------|

| | |
|--------------|------------------------------------|
| Stack Height | 5 mm, 8 mm, 9 mm, 11 mm, 16 mm, 22 |
|--------------|------------------------------------|



mm, 25 mm, 30 mm[1.181 in]

PCB Thickness (Recommended)

.06 mm[.25 in]

Usage Conditions

Operating Temperature Range

-65 – 125 °C[-85 – 257 °F]

Operation/Application

Assembly Process Feature

None

Circuit Application

Power & Signal

Industry Standards

UL Flammability Rating

UL 94V-0

Packaging Features

Packaging Quantity

56

Packaging Type

Box, Tray

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1658013-2
MSB0.80PL5ASY56DP,-,10,VCTY



TE Part # 1-1658014-2
MSB0.80PL8ASY56DP,-,10,VCTY



TE Part # 1-1658015-2
MSB0.80PL11ASY56DP,-,10,VCTY



TE Part # 1-1658016-2
MSB0.80PL16ASY56DP,-,10,VCTY




TE Part # 1-1658017-2
MSB0.80PL19ASY56DP,-,10,VCTY



TE Part # 1-1658019-2
MSB0.80PL25ASY56DP,-,10,VCTY



TE Part # 1-1658020-2
MSB0.80PL30ASY56DP,-,10,VCTY



TE Part # 1-1658438-2
MSB0.80PL14ASY56DP,-,10,VCTY



TE Part # 1-1658018-2
MSB0.80PL22ASY56DP,-,10,VCTY

Documents

Product Drawings

[MSB0.80RC-ASY56DP,-,10,VCTY](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-1658012-2_P.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1658012-2_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1658012-2_P.3d_stp.zip](#)



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MICTOR SB CONNECTORS

English

Product Specifications

Application Specification

English