



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Hardware Type: **Jackscrew Kit**

Jackscrew Type: **Turnable**

Jackscrew Style: **Female**

Features

Product Type Features

Strain Relief	Without
Product Type	Hardware

Body Features

Material	Zinc Alloy
Thread Lead Type	Double

Mechanical Attachment

Jackscrew Material	Zinc Alloy
Jackscrew Finish	Non-Hexavalent Chromate
Mounting Hardware	Jackscrew Pin
Screw & Hole Thread Size	6-32 [M3.5 x .6]
Hardware Type	Jackscrew Kit
Jackscrew Type	Turnable
Jackscrew Style	Female

Dimensions

Height	7.92 mm[.312 in]
Length	43.26 mm[2.188 in]
Width	7.92 mm[.312 in]

Operation/Application

For Use With	12 Position High Current Connectors, 15,16, and 42-Position Mixed Connectors, 20 and 28-Position High Voltage Connectors, 20, 26, 34, 41 and 50 Position Posted
--------------	---



Connectors, 20, 26, 34, 41 and 50 Position
Standard Connectors

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Other

Comment	Two required., Use turnable jackscrews on mating housings when mating to grounding block.
---------	---

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | [AMP M Series](#)



Board-to-Board Jumpers & Shunts(7)




Rack & Panel Connectors(1)



Rectangular Connector Hardware(52)



Rectangular Power Connectors(66)



Standard Edge Connectors(2)

Documents

Product Drawings

[SERIES "M" JACKSCREW FEM. ASSY](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-200867-1_W.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-200867-1_W.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-200867-1_W.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English