

1-1801178-6 ✓ ACTIVE

TE Internal #: 1-1801178-6

Housing for Female Terminals, Wire-to-Wire, 3 Position, .13 in [3.33 mm] Centerline, Sealable, Black, Signal, Cable Mount (Free-Hanging)

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Housings



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **1.5 mm [.059 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **3**

Centerline (Pitch): **3.33 mm [.13 in]**

Features

Product Type Features

Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	16 VDC
Nominal Voltage Architecture	16 V

Body Features

Cable Exit Angle	180°
------------------	------



Body Material	PBT GF
---------------	--------

Primary Product Color	Black
-----------------------	-------

Connector Code	6
----------------	---

Contact Features

Contact Size	1.5mm
--------------	-------

Contact Type	Receptacle
--------------	------------

Mating Tab Width	1.5 mm [.059 in]
------------------	------------------

Mechanical Attachment

Mounting Feature	Without
------------------	---------

Terminal Position Assurance	No
-----------------------------	----

Strain Relief	Without
---------------	---------

Mating Alignment Type	Keyed
-----------------------	-------

Mating Alignment	With
------------------	------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	3.33 mm [.13 in]
--------------------	------------------

Dimensions

Product Width	39.05 mm [1.53 in]
---------------	--------------------

Product Length	21.33 mm [.839 in]
----------------	--------------------

Product Height	19.65 mm [.773 in]
----------------	--------------------

Usage Conditions

Operating Temperature (Max)	150 °C [302 °F]
-----------------------------	-----------------

Operating Temperature Range	-40 – 150 °C [-40 – 302 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	528
--------------------	-----

Packaging Method	Box
------------------	-----

Other

Serviceable	No
-------------	----

Connector Position Assurance Capable	Yes
--------------------------------------	-----



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

			
<p>TE Part # CAT-AM706-T273 AMP MCP, SFC, RECEPTACLE</p>	<p>TE Part # 1801467-1 COVER, FIXED, 3 WAY HP CONNECTOR</p>	<p>TE Part # 1-1579008-0 EXTRACTION TOOL TO OPEN SECONDARY LOCK</p>	<p>TE Part # 1-1801168-5 COVER FOR 3W HP CONNECTOR</p>



TE Part # 1-1801467-1
COVER, FIXED, 3 WAY HP
CONNECTOR



TE Part # 1-1801467-2
COVER, FIXED, 3 WAY HP
CONNECTOR



TE Part # 1801168-5
COVER FOR 3W HP CONNECTOR



TE Part # 1801177-6
3W TAB CONNECTOR HP BROWN



TE Part # 1801359-1
ADAPTER, ROTATIVE COVER FOR 3W
CONN



TE Part # 1801467-2
COVER, FIXED, 3 WAY HP
CONNECTOR



TE Part # 1801468-1
COVER, ROTATIVE, 3 WAY HP
CONNECTOR



TE Part # 6-1579018-2
EXTRACTION TOOL

Documents

Product Drawings

3W RECEPTACLE HP CONNECTOR BROWN

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-1801178-6_F.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1801178-6_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1801178-6_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English