



TE Internal #: 1-2273034-1
M8/M12 Cable Assemblies, Sensor/Actuator, 5 Position, A Keying
Code, M12 Socket, M12 Pigtail, Straight Connector Orientation
(End A), Length 1.5 m
[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M12 A-Code Male Straight Pigtail



M8/M12 Application Type: **Sensor/Actuator**
Number of Positions: **5**
Keying Code: **A**
Connector Type (End A): **M12 Socket**
Cable Assembly Type: **M12 Pigtail**
[All M12 A-Code Male Straight Pigtail \(56\)](#)

Features

Product Type Features

Product Type	Cable Assembly
Cable Type	PVC
Assembly Type	Pigtail
Connector Type (End A)	M12 Socket
Cable Assembly Type	M12 Pigtail

Configuration Features

Number of Positions	5
Keying Code	A

Electrical Characteristics

Operating Voltage	125 VDC
-------------------	---------

Body Features

Cable Exit Angle	Straight
Environmental Protection	With
Connector Color	Blue
Wire Color	Brown, White, Blue, Black, Green/Yellow
Cable Jacket Color	Black



Insulation Material	PVC
Contact Features	
Contact Current Rating	4 A
Mechanical Attachment	
Screw & Hole Thread Size	M12
Connector Orientation (End A)	Straight
Housing Features	
Housing Material	Plastic
Dimensions	
Overall Outside Cable Diameter	5.2 mm[.204 in]
Wire Size	.326 mm²
Usage Conditions	
Operating Temperature Range	-30 – 80 °C[-22 – 176 °F]
Operation/Application	
M8/M12 Application Type	Sensor/Actuator
Shielded	No
Packaging Features	
Packaging Method	Box
Packaging Quantity	25
Other	
Field Serviceable	Yes
Cable Assembly Length	1.5 m
Cable Assembly Configuration	Single Ended

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223)



	Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

M12 x 1.0 straight plug pigt A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2273034-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2273034-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2273034-1_A.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

CONNECTIVITY SOLUTIONS FOR INFOTAINMENT APPLICATIONS

English

Product Specifications

Application Specification

English