



**M12 Rail Right Angle**

TE Internal #: 1-2823588-1

Standard Circular Connectors, Cable-to-Cable, 4 Position, Sealable, Wire & Cable, Signal, Cable Mount (Free-Hanging), Nickel, M12 Rail Right Angle

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > M12 R/A CRIMPED STRAIN RELIEF



Connector System: **Cable-to-Cable**

Number of Positions: **4**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **4 A**

[All M12 R/A CRIMPED STRAIN RELIEF \(12\)](#)

**Features**

**Product Type Features**

Product Type	Connector Kit
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Full Metal Shell

**Configuration Features**

Number of Positions	4
Contacts Preloaded	No

**Electrical Characteristics**

Operating Voltage	50 VDC
-------------------	--------

**Body Features**

Environmental Protection	Yes
Weight	25 g[.0552 lb]
Environmental Protection Type	Elastomer Sealed
Shell Plating Material	Nickel



Shell Base Material	Brass
Circular Connector Insulation Material Type	Low Fire Hazard Thermoplastic
Hermetically Sealed	Yes

#### Contact Features

Contact Current Rating (Max)	4 A
Circular Connector Contact Type	Pin

#### Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
Polarization Code	D
Mating Alignment Type	Keyed
Mating Retention	With

#### Dimensions

Accepts Wire Insulation Diameter Range	7.3 mm
Wire Size	22 AWG

#### Usage Conditions

IP Dust Sealing Level	6
IP Water Sealing Level	7
Operating Temperature Range	-40 – 70 °C, -40 – 85 °C[-40 – 158 °F][-40 – 185 °F]

#### Operation/Application

Durability Rating	250 Cycles
Circuit Application	Signal
Shielded	Yes

#### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

#### Packaging Features

Packaging Quantity	1
--------------------	---

#### Other

Field Serviceable	Yes
-------------------	-----

#### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>



EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (3.5% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1-2823557-1  
CRIMP TOOL FOR CRIMP FLANGE /SLEEVE



TE Part # 1-2823560-1  
ASSEMBLY TOOL HANDLE FOR CRIMP FLANGE




TE Part # 1-2823561-1  
UNIVERSAL INSERT (ALL M12 CODES)



TE Part # CAT-M1-M1  
M12 ASSEMBLY TOOLING



## Also in the Series | M12 Rail Right Angle



## Documents

### Product Drawings

M12 D-90 DEGR-M-4,CAT 5 RADOX 7.3MM, H&S

English

### CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-2823588-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2823588-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2823588-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

M12 Right Angled Connector

English

### Product Specifications

Product Specification

English

1-2823588-1

Standard Circular Connectors, Cable-to-Cable, 4 Position, Sealable, Wire & Cable,  
Signal, Cable Mount (Free-Hanging), Nickel, M12 Rail Right Angle

