

STRATO-THERM DIAMOND GRIP


TE Internal #: 1-322325-0

Splices, 22 – 16 AWG Wire Size, .26 – 1.65 mm² Wire Size, Strap, .51 – 3.26 kcmil Wire Size, 509 – 3260 CMA Wire Size, STRATO-THERM DIAMOND GRIP

[View on TE.com >](#)



Terminals & Splices > Splices



Wire Size: .26 – 1.65 mm²

Sealable: No

Splice Features: Strap

Accepts Wire Insulation Diameter Range: 3.55 mm [.14 in]

Features

Product Type Features

Discrete Wire Type	Stranded
Sealable	No
Splice Type	Butt Splice
Serrated	Yes
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Weight per Piece	1 g
Plating Material	Unplated
Splice Features	Strap
Primary Product Material	Alumel
Primary Product Color	Green

Contact Features

Barrel Type	Closed
-------------	--------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Wire Size	509 – 3260 CMA
Accepts Wire Insulation Diameter Range	3.55 mm[.14 in]
Overall Product Length	22.58 mm[.889 in]

Usage Conditions

High Temperature Rating	649 °C[1200 °F]
Insulation Option	Uninsulated
Operating Temperature Range	649 °C[1200 °F]

Operation/Application

Heavy Duty	No
Compatible With Wire Base Material	Copper

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Other

Military Category	No
-------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

REPRESENTATION ONLY

TE Part # 46673
DAHT STRATO 22-16 ASSY

REPRESENTATION ONLY

TE Part # 46673-1
DAHT STRATO 22-16 ASSY

Also in the Series | STRATO-THERM DIAMOND GRIP

Knife Disconnects(5)

Ring Terminals & Spade Terminals(73)

Splices(10)

Documents

Product Drawings
DG 22-16 HT ALUMEL BUTT
English

CAD Files
Customer View Model
ENG_CVM_CVM_1-322325-0_F.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-322325-0_F.3d_igs.zip
English



Customer View Model

[ENG_CVM_CVM_1-322325-0_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English