




Cable Assemblies > RF Cable Assemblies



Number of Positions: 17

### Features

#### Product Type Features

Coax Cable Type	Coaxial Ribbon Cable
-----------------	----------------------

#### Configuration Features

Number of Positions	17
---------------------	----

### Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 226733-2  
RIBBON COAX CONN ASSY 5 POS



TE Part # 226733-7  
RIBBON COAX CONN ASSY 10 POS



TE Part # 10226733-00  
QDCC-0600010001: CTO-12000000-07



TE Part # 2267339-1  
2MM SHUNT HOUSING - BLK



TE Part # 2267339-2  
2MM SHUNT HOUSING - BLUE



TE Part # 2267339-3  
2MM SHUNT HOUSING - RED

## Documents

### Product Drawings

#### RIBBON COAX CONN ASSY 17 POS

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-226733-4\\_G\\_c-1-226733-4-g.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-226733-4\\_G\\_c-1-226733-4-g.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-226733-4\\_G\\_c-1-226733-4-g.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Instruction Sheets

#### AMP\* RIBBON CABLE RECEPTACLE KITS (FOR AMP RIBBON CABLES 226298, 22646)

English

#### Instruction Sheet (U.S.)

English



[Agency Approvals](#)

[Agency Approval Document](#)

English