



TE Internal #: 1-2825272-6
 Standard Rectangular Connectors, Connector Assembly, Plug,
 Mating Alignment, Keyed Mating Alignment Type, Mating
 Retention, Vertical

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Plug**

Mating Alignment: **With**

Mating Alignment Type: **Keyed**

Mating Retention: **With**

Features

Product Type Features

Connector Type	Header
Glow Wire Rating	Glow Wire
Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Insertion Force Type	Normal
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Signal Positions	16
PCB Mount Orientation	Vertical
Number of Positions	16
Number of Rows	2

Electrical Characteristics

--	--



Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Transmits (Typical)	Signal (Data)
Contact Layout	Matrix
Contact Type	Pin
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin
Contact Retention Within Housing	With
Contact Current Rating (Max)	13 A

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

PCB Mount Alignment	Without
Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With
Mating Retention Type	Latch
PCB Mount Retention	Without
Connector Mounting Type	Board Mount

Housing Features

Housing Material	Polyamide
Housing Color	White
Centerline (Pitch)	4.19 mm[.165 in]

Dimensions

Insulation Diameter (Max)	2.39 mm
PCB Thickness (Recommended)	1.6 mm[.063 in]
Height	12.8 mm[.504 in]
Length	34.8 mm[1.37 in]
Width	9.75 mm[.383 in]
Tail Length	3.5 mm[.138 in]
Accepts Wire Insulation Diameter Range	1.2 – 3.1 mm[.047 – .122 in]
Wire Size	.12 – 1.4 mm ²



Row-to-Row Spacing	4.2 mm[.165 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Halogen Free	Yes
--------------	-----

Shielded	No
----------	----

Circuit Application	Signal
---------------------	--------

Identification Marking

Circuit Identification Feature	With
--------------------------------	------

Industry Standards

Agency/Standard	CSA, UL
-----------------	---------

UL Rating	Recognized
-----------	------------

CSA File Number	208567
-----------------	--------

UL File Number	E28476
----------------	--------

CSA Rating	208567
------------	--------

VDE Tested	No
------------	----

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	165
--------------------	-----

Packaging Method	Box & Tray, Tray
------------------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Not Yet Reviewed
-----------------------------	------------------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1586768-8
8P VERT HDR VAL-U-LOK GW



TE Part # 1-1586768-4
14P VERT HDR VAL-U-LOK GW



TE Part # 1-1586768-6
16P VERT HDR VAL-U-LOK GW




TE Part # 1-1586768-8
18P VERT HDR VAL-U-LOK GW



TE Part # 1-1586863-6
16P VAL-U-LOK R/A HDR GW



TE Part # 1-2029059-6
16P VAL-U-LOK VRTHDR W/PGS GW




TE Part # 1-2029172-6
16P VRT HDR VAL-U-LOK V2 W/ODH




TE Part # 1-2825272-4
14P VERT HDR VAL-U-LOK HCS GW




TE Part # 1-2825272-8
18P VERT HDR VAL-U-LOK HCS GW



TE Part # 2-1586768-2
22P VERT HDR VAL-U-LOK GW



TE Part # 2-2825272-0
20P VERT HDR VAL-U-LOK HCS GW



TE Part # 2-2825272-2
22P VERT HDR VAL-U-LOK HCS GW



Documents

Product Drawings

[16P VERT HDR VAL-U-LOK HCS GW](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-2825272-6_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2825272-6_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2825272-6_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL](#)

English