

1-5229913-1 ✓ ACTIVE

## CHAMP | CHAMP Docking Connectors


TE Internal #: 1-5229913-1

IDC D-Sub Connectors, Receptacle, 26 – 24 AWG Solid Wire Size, .13 – .32 mm<sup>2</sup> Solid Wire Size, 24 AWG Stranded Wire, CHAMP Docking Connectors

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Receptacle Kit, Signal, 50, 2.16 mm



Connector & Housing Type: **Receptacle**

Solid Wire Size: **.13 – .32 mm<sup>2</sup>**

Stranded Wire Size: **.33 mm<sup>2</sup>**

[All IDC D-Sub: Receptacle Kit, Signal, 50, 2.16 mm \(10\)](#)

## Features

### Product Type Features

Profile	Standard
Connector Classification	IDC
Slot Type Letter Code	B
Product Category	Connectors
Protective Cover	With
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board, Cable-to-Cable
Connector Product Type	Connector Kit
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	50
Number of Rows	2
Compatible With Wire & Cable Type	Discrete Wire, Round Jacketed Cable



### Body Features

Color	Black
Cover Material	Polyethylene, Polyphenylene Oxide

### Contact Features

Contact Mating Area Plating Thickness	.76 µm[30 µin]
Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel
Contact Underplating Material	Palladium Nickel
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	.5 A, 1 A

### Mechanical Attachment

Mating Connector Lock	With
Mating Connector Lock Type	Screwlocks
Panel Mount Feature	Without
Screw & Hole Thread Size	4-40
Connector Mounting Type	Cable Mount (Free-Hanging)

### Housing Features

Housing Material	Polyphenylene Oxide
Housing Color Dot Designation	Blue
Centerline (Pitch)	2.16 mm[.085 in]

### Dimensions

Cable Outside Diameter	8.89 – 10.8 mm[.35 – .425 in]
Insulation Diameter (Max)	1.14 mm[.045 in]
Accepts Cable Diameter (Max)	10.8 mm[.425 in]
Solid Wire Size	.13 – .32 mm <sup>2</sup>
Stranded Wire Size	.33 mm <sup>2</sup>
Wire Size	24 AWG

### Usage Conditions

Operating Temperature Range	-40 – 75 °C[-40 – 167 °F]
-----------------------------	---------------------------

### Operation/Application

Shielded	Yes
Circuit Application	Signal

### Packaging Features



Packaging Method	Bag
Packaging Quantity	1

### Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

 <p>TE Part # CAT-357-D601 IDC D-Sub: Receptacle Assembly, Signal, 2.16 mm</p>	 <p>TE Part # CAT-357-D658 IDC D-Sub: Plug Assembly, Signal, Cable to Cable, 2.16 mm</p>	 <p>TE Part # 229378-1 ASSY, MI-1 TOOL, STD 14-50 POSN</p>
---	---	---

### Also in the Series | CHAMP Docking Connectors



D-Sub Covers(28)



D-Sub Locking &amp; Mounting(29)



Docking Connector Guide Hardware(5)



Docking Connectors(31)



IDC D-Sub Connectors(79)



PCB D-Sub Connectors(1)

## Documents

### Product Drawings

[KIT, RCPT, 50 POS, B SLOT](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_1-5229913-1\\_O.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1-5229913-1\\_O.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-5229913-1\\_O.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.