



Connectors > RF Coax Connectors > RF Connectors



RF Interface: **BNC**

RF Connector Style: **Plug**

RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**

Impedance: **75 Ω**

Compatible With RF Cable Type: **JIS 3C-2V**

Features

Product Type Features

Connector Shape	Circular
Connector Seal Type	Gasket
RF Interface	BNC
RF Connector Style	Plug
Compatible With RF Cable Type	JIS 3C-2V
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	75 Ω
-----------	------

Body Features

Cable Connector Orientation	Straight
Body Material	Brass
Body Material Finish	Passivated
Body Plating Material	Nickel

Contact Features

RF Connector Center Contact Underplating Material	Nickel
---	--------



	1080 µin
Crimp Type	Hex
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Cable Mount (Free-Hanging)
RF Contact Captivation Method	Mechanical
Detent	With

Dimensions

RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]
---	-------------------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Operation/Application

Operating Frequency	2 GHz
---------------------	-------

Packaging Features

Packaging Quantity	25
Packaging Method	Carton

Other

Coupling Nut Base Material	Brass
Grade	Commercial
Dielectric Material	Polymethylpentene

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2022
(224)
Candidate List Declared Against: JAN 2021
(211)
SVHC > Threshold:
Pb (3.7% in Component part)
Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-076-BNCJKRA75C BNC RF Connector: Jack, Right-Angle, 75 Ohm	TE Part # 5222132-1 JACK,VERTICAL,PCB,75 OHM,BNC	TE Part # 1-1634622-0 BNC Ins R/A PCB Skt 75Ohm Black	TE Part # 5221221-5 JACK BLKHD 75OHM BNC
TE Part # 5414217-1 BNC SOLDER RCPT	TE Part # 5413558-1 JACK,RTANG,PCB,75 OHM,BNC	TE Part # 1-1478052-0 BNC Pnl Plg 75Ohm Silver Pltd	TE Part # 58425-1 DIE,COAX 213/255X042 SQ IS9657





TE Part # 58531-1
AMP PRO-CRIMPER ASSEMBLY



TE Part # 2016080-2
JACK,PCB,COMMERCIAL BNC



TE Part # 6274291-1
JACK,PCB,COML BNC, 75OHM



TE Part # 5221244-1
SOLDER RCPT,75 OHM,COML BNC

Documents

Product Drawings
KIT PLUG 75 OHM BNC HEX CRIMP
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-5413589-1_C.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1-5413589-1_C.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1-5413589-1_C.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages
BNC Connectors
English

Product Specifications
Application Specification
English

Product Environmental Compliance
Product Compliance
English
Product Compliance
English

Instruction Sheets
Instruction Sheet (U.S.)
English

