



Connectors > RF Coax Connectors > RF Coax Accessories > RF Connector Hardware



RF Connector Hardware Type: Jam Nut

Features

Product Type Features

RF Connector Hardware Type	Jam Nut
----------------------------	---------

Body Features

Primary Product Material	Brass
Body Plating Material	Silver

Packaging Features

Packaging Quantity	1000
Packaging Method	Box & Carton

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-076-BNCRABAY BNC RF Connector: Male (Jack), Right Angle	 TE Part # CAT-076-BNCVTBAY BNC Vertical Jack RF Connector, 50 Ohm, Bayonet Coupling Mechanism	 TE Part # 5414168-3 JACK,BULKHEAD,COM'L TNC	 TE Part # 5413771-3 JACK BLKHD,COML BNC,HEX CRIMP
 TE Part # 5227839-1 TNC PCB RT ANGLE JACK	 TE Part # 227223-1 PANEL INSULATING BUSHING	 TE Part # 330620 INSUL BUSHING BNC BLKHD PHEN	 TE Part # 5228980-7 JACK,BHD,COML,SERIES BNC,GOLD
 TE Part # 5227426-1 BNC BLKHD RECPT SEALED	 TE Part # 5225398-7 BNC DUAL CRIMP JACJ	 TE Part # 1-329632-2 LOCKWASHER, PLATED	 TE Part # 5227820-1 TNC PCB VERT



TE Part # 5413506-1
JACK,RTANG,PCB,75 OHM,TNC

TE Part # 1-5225398-5
DUAL CRIMP BNC BLKHD JACK

TE Part # 1057676-1
3104 7941 00

TE Part # 1057679-1
3104 7985 00

TE Part # 5414105-1
JACK,ADAPTER,BHD,ISOLATED BNC

Documents

Product Drawings

JAM NUT, PLATED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-329631-2_AP.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-329631-2_AP.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-329631-2_AP.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BNC Connectors

English

Product Environmental Compliance

MD_1-329631-2

English

MD_1-329631-2

English

