



AMP-TY

TE Internal #: 1-603230-9

Cable Ties, Identification, Bag, 80.067 Newton Tensile Strength, 18 lbf Tensile Strength, Product Length 4.34 in [110 mm]

[View on TE.com >](#)

Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Identification**

Packaging Method: **Bag**

Tensile Strength: **80.067 Newton**

Product Length: **110 mm [ 4.34 in ]**

**Features**

**Product Type Features**

Product Type	Cable Tie
Shape	TY-003
Cable Tie Style	Identification
Tensile Strength	80.067 Newton

**Body Features**

Primary Product Color	Natural
Primary Product Material	Nylon

**Dimensions**

Bundle Range Diameter	19.1 mm[.75 in]
Product Length	110 mm[4.34 in]
Product Width	2.46 mm[.097 in]
Product Thickness	.94 mm[.037 in]

**Identification Marking**

Marking Pad Size	18.69 x 7.80 mm[.736 x .307 in]
------------------	---------------------------------

**Packaging Features**

Packaging Method	Bag
Packaging Quantity	100

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



### Documents

**Product Drawings**

CABLE TIE FLAG,NAT,100PK

English

**Datasheets & Catalog Pages**

CABLE TIES

English

1-603230-9

Cable Ties, Identification, Bag, 80.067 Newton Tensile Strength, 18 lbf Tensile Strength, Product Length 4.34 in [110 mm]

