



TE Internal #: 1-5331677-3
Pin Sockets, Socket Length 3.51 mm [.138 in], PCB Hole Diameter .062 in [1.57 mm], Closed Bottom, .41 – .518 mm² Wire Size, 20 – 21 AWG Wire Size
[View on TE.com >](#)

Connectors > Socket Connectors > Pin Sockets > Miniature Spring Sockets: Closed Bottom, Beryllium Copper, 5A



Socket Length: 3.51 mm [.138 in]
PCB Hole Diameter: 1.57 mm [.062 in]
Socket Sleeve Style: Closed Bottom
Wire Size: .41 – .518 mm²

[All Miniature Spring Sockets: Closed Bottom, Beryllium Copper, 5A \(11\)](#)

Features

Product Type Features

Socket Sleeve Style	Closed Bottom
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Sleeve Material	Copper
Sleeve Plating Material	Tin

Contact Features

Contact Spring Plating Material	Tin
Contact Spring Plating Thickness	2.54 µm[30 µin]
Contact Mating Area Plating Material Thickness	2.54 µm
Contact Base Material	Beryllium Copper
Contact Current Rating (Max)	5 A

Termination Features

Insertion Method	Hand/Semi-Automatic/Automatic
Termination Method to Printed Circuit Board	Through Hole - Press-Fit



Termination Method to Wire & Cable	Solder
------------------------------------	--------

Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm[.031 – .125 in]
Socket Length	3.51 mm[.138 in]
PCB Hole Diameter	1.57 mm[.062 in]
Wire Size	.41 – .518 mm²
Mating Pin Diameter Range	.76 – .84 mm[.03 – .033 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Solder Process Feature	None
Circuit Application	Power & Signal

Packaging Features

Packaging Quantity	2000
Packaging Method	Bag, Loose Piece

Other

Spring Material	Beryllium Copper
-----------------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-332070-4
SOCKET,MIN-SPR W/H AU SER-4



TE Part # CAT-377-MSSCB65
Miniature Spring Sockets: Closed Bottom, Beryllium Copper, 6.5A



TE Part # 1-332070-7
SOCKET,MIN-SPR W/KO AU SER-4



TE Part # 1-5331677-6
SOCKET,MIN-SPR SN SER-3



TE Part # 2-332070-1
SOCKET,MIN-SPR SN-AU SER-4

Documents

Product Drawings
SOCKET,MIN-SPR SN SER-3U SER-3
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-5331677-3_O.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1-5331677-3_O.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1-5331677-3_O.3d_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English