



AMP-TY

TE Internal #: 1-603227-9

Cable Ties, Standard, Bag, 133.5 Newton Tensile Strength, 30 lbf Tensile Strength, Product Length .312 in [7.99 mm], Product Width .142 in [3.6 mm]

[View on TE.com >](#)

Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**
Packaging Method: **Bag**
Tensile Strength: **133.5 Newton**
Product Length: **7.99 mm [.312 in]**

Features

Product Type Features

Product Type	Accessory
Accessory Type	Cable Clamp
Cable Tie Style	Standard
Tensile Strength	133.5 Newton

Body Features

Primary Product Color	Natural
Primary Product Material	Nylon

Dimensions

Bundle Range Diameter	31.75 mm[1.25 in]
Product Length	7.99 mm[.312 in]
Product Width	3.6 mm[.142 in]
Product Thickness	1.1 mm[.043 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 734587-1
CABLE TY TOOL



TE Part # 4-1579002-9
CABLE TIE TOOL

Documents

Product Drawings
CABLE TIE, NAT, 6" L, 100/PACK
English

Datasheets & Catalog Pages
CABLE TIES
English

Instruction Sheets
Instruction Sheet (U.S.)

1-603227-9

Cable Ties, Standard, Bag, 133.5 Newton Tensile Strength, 30 lbf Tensile Strength,
Product Length .312 in [7.99 mm], Product Width .142 in [3.6 mm]



English