

1-650930-4 ✓ ACTIVE

EUROCARD | Eurocard Type R


TE Internal #: 1-650930-4

Eurocard Connectors, Plug, Board-to-Board, 64 Position, .1 in [2.54 mm] Centerline, Printed Circuit Board, 2 Row, Vertical, 32 Column, Eurocard Type R

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Plug**

Connector System: **Board-to-Board**

Termination Post & Tail Length: **13.23 mm [ .521 in ]**

Number of Positions: **64**

Centerline (Pitch): **2.54 mm [ .1 in ]**

## Features

### Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| Connector & Housing Type          | Plug                  |
| Connector System                  | Board-to-Board        |
| Sealable                          | No                    |
| Connector & Contact Terminates To | Printed Circuit Board |
| DIN Size                          | Half                  |
| DIN Level                         | II                    |

### Configuration Features

|                                      |          |
|--------------------------------------|----------|
| Number of Positions                  | 64       |
| Number of Rows                       | 2        |
| PCB Mount Orientation                | Vertical |
| Number of Columns                    | 32       |
| Number of Power or Coaxial Positions | 64       |
| Number of Signal Positions           | 64       |
| Rows Loaded                          | A, C     |



### Electrical Characteristics

|                   |         |
|-------------------|---------|
| Operating Voltage | 250 VAC |
|-------------------|---------|

### Contact Features

|   |  |
|---|--|
| Contact Cross Section                                   | .64 x .64 mm [.025 x .025 in]            |
| PCB Contact Termination Area Plating Material Thickness | 2.54 – 5.08 $\mu$ m [100 – 200 $\mu$ in] |
| Contact Type  | Pin                                      |
| Contact Mating Area Plating Material Thickness          | .76 $\mu$ m [30 $\mu$ in]                |
| Contact Mating Area Plating Material                    | Gold                                     |
| PCB Contact Termination Area Plating Material           | Tin-Lead                                 |
| Contact Base Material                                   | Phosphor Bronze                          |
| Contact Current Rating (Max)                            | 3 A                                      |

### Termination Features

|   |                          |
|---|--------------------------|
| Termination Method to Printed Circuit Board | Through Hole - Press-Fit |
| Termination Post & Tail Length              | 13.23 mm [.521 in]       |

### Mechanical Attachment

|                          |                       |
|--------------------------|-----------------------|
| Mating Alignment Type    | Polarization          |
| Mating Alignment         | With                  |
| PCB Mount Alignment      | Without               |
| PCB Mount Retention      | With                  |
| PCB Mount Retention Type | Action/Compliant Tail |
| Connector Mounting Type  | Board Mount           |

### Housing Features

|                    |                 |
|--------------------|-----------------|
| Housing Material   | Polyester - GF  |
| Housing Color      | Gray            |
| Centerline (Pitch) | 2.54 mm [.1 in] |

### Dimensions

|                             |                    |
|-----------------------------|--------------------|
| Connector Height            | 11.51 mm [.453 in] |
| PCB Thickness (Recommended) | 2.36 mm [.093 in]  |
| Row-to-Row Spacing          | 2.54 mm [.1 in]    |

### Usage Conditions

|                             |                             |
|-----------------------------|-----------------------------|
| Operating Temperature Range | -55 – 105 °C [-67 – 221 °F] |
|-----------------------------|-----------------------------|

### Operation/Application



|          |    |
|----------|----|
| Shielded | No |
|----------|----|

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

### Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

### Packaging Features

|                  |     |
|------------------|-----|
| Packaging Method | Box |
|------------------|-----|

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                              |           |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|

|                             |           |
|-----------------------------|-----------|
| EU ELV Directive 2000/53/EC | Compliant |
|-----------------------------|-----------|

|   |   |
|---|---|
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
|---|---|

|  |   |
|--|---|
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
|--|---|

|                 |  |
|-----------------|--|
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
|-----------------|--|

|                           |  |
|---------------------------|--|
| Solder Process Capability | Not applicable for solder process capability |
|---------------------------|--|



#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | Eurocard Type R



## Documents

### Product Drawings

#### 064 EURO TYPE R PIN AP ASSY

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1-650930-4\\_P.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-650930-4\\_P.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-650930-4\\_P.3d\\_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Product Specifications](#)

[Application Specification](#)

English