




AMP | AMP Type III+

TE Internal #: 1-66103-7

Power Contacts, Contact, Precious Metal, 24 – 20 AWG Wire Size, .2 – .6 mm<sup>2</sup> Wire Size, Wire & Cable, Crimp, Power & Signal, Pin, AMP Type III+

[View on TE.com >](#)

Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**  
Contact Mating Area Plating Material: **Precious Metal**  
Wire Size: **.2 – .6 mm<sup>2</sup>**  
Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

|                                   |              |
|-----------------------------------|--------------|
| Power Contact Type                | Contact      |
| Connector & Contact Terminates To | Wire & Cable |

Electrical Characteristics

|              |      |
|--------------|------|
| Test Current | 13 A |
|--------------|------|

Contact Features

|                                                       |                  |
|-------------------------------------------------------|------------------|
| Contact Mating Area Plating Material                  | Precious Metal   |
| Contact Current Rating (Max)                          | 13 A             |
| Contact Type                                          | Pin              |
| Mating Pin Diameter                                   | 1.57 mm[.062 in] |
| Contact Base Material                                 | Brass            |
| Contact Mating Area Plating Material Thickness        | .76 μm[30 μin]   |
| Wire Contact Termination Area Plating Thickness       | 1.27 μm[50 μin]  |
| Wire Contact Termination Area Plating Material        | Tin              |
| Wire Contact Termination Area Plating Material Finish | Bright           |
| Contact Orientation                                   | Straight         |



|                                         |                 |
|-----------------------------------------|-----------------|
| Contact Underplating Material           | Nickel          |
| Contact Underplating Material Thickness | 1.27 µm[50 µin] |
| Contact Size                            | 16              |

Termination Features

|                                    |       |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

Mechanical Attachment

|                         |      |
|-------------------------|------|
| Wire Insulation Support | With |
|-------------------------|------|

Dimensions

|                                        |                              |
|----------------------------------------|------------------------------|
| Wire Size                              | .2 – .6 mm²                  |
| Accepts Wire Insulation Diameter Range | 1.02 – 2.03 mm[.04 – .08 in] |

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -55 – 90 °C[-67 – 194 °F] |
|-----------------------------|---------------------------|

Operation/Application

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Packaging Features

|                    |                  |
|--------------------|------------------|
| Packaging Method   | Box, Loose Piece |
| Packaging Quantity | 100              |

Other

|                 |                                                          |
|-----------------|----------------------------------------------------------|
| Wire/Cable Type | Discrete Wire                                            |
| For Use With    | CPC Connectors, G Series Connectors, M Series Connectors |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC                                                  |



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 91515-1  
CCII TYPE III+ MNL PIN SKT 30-20 ASSY

TE Part # 58495-2  
PROCRIMPER DIE ASSY MULTIMATE

TE Part # 200893-2  
INSERTION TOOL CONT

TE Part # 58495-1  
PRO CRIMPER ASSY MULTIMATE

TE Part # 539972-1  
EXTRACTION TOOL

TE Part # 305183  
EXTRACT TOOL TYPE 2 20-16

TE Part # 91505-1  
CCII TYPE III+ 24-16 ASSY

TE Part # 169400  
CERTI-LOK FRAME W/O DIES

Also in the Series | AMP Type III+

Insertion & Extraction Tools(4)

Power Contacts(410)

Documents





Product Drawings

III+ PIN,24-20, 30AU/SN,SMPACK

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1-66103-7\_AL.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-66103-7\_AL.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-66103-7\_AL.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

Japanese

Instruction Sheet (U.S.)

English