

1-747943-6 ✓ ACTIVE

AMPLIMITE | AMPLIMITE HDE


TE Internal #: 1-747943-6

IDC D-Sub Connectors, Receptacle, 26 – 22 AWG Solid Wire Size, .13 – .32 mm² Solid Wire Size, Shielded, Cable-to-Cable, 9 Position, AMPLIMITE HDE

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Receptacle Kit, Wire to Wire, Signal, 2.74 mm



Connector & Housing Type: **Receptacle**

Solid Wire Size: **.13 – .32 mm²**

Shielded: **Yes**

Connector System: **Cable-to-Cable**

[All IDC D-Sub: Receptacle Kit, Wire to Wire, Signal, 2.74 mm \(8\)](#)

Features

Product Type Features

Grade	Standard
Grounding Indents	Without
Enclosure Material	PVC
Shell Type	Front Metal Shell
Connector & Housing Type	Receptacle
Connector System	Cable-to-Cable
Connector Product Type	Connector Kit
D-Sub Shell Size	1
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Pre-Assembled	No
Number of Positions	9



Number of Rows	2
----------------	---

Compatible With Wire & Cable Type	Discrete Wire, Round Jacketed Cable
-----------------------------------	-------------------------------------

Body Features

Shield Material	Steel
-----------------	-------

Color	Black
-------	-------

Shell Material	Steel
----------------	-------

Insert Material	Thermoplastic
-----------------	---------------

Shell Plating Material	Tin
------------------------	-----

Shield Plating Material	Tin
-------------------------	-----

Contact Features

Contact Type	Socket
--------------	--------

Contact Mating Area Plating Thickness	.76 μm[30 μin]
---------------------------------------	----------------

Contact Mating Area Plating Material	Gold
--------------------------------------	------

Contact Underplating Material	Nickel
-------------------------------	--------

PCB Contact Termination Area Plating Material	Tin
---	-----

Contact Base Material	Phosphor Bronze
-----------------------	-----------------

D-Sub Contact Size	20
--------------------	----

Contact Current Rating (Max)	5 A
------------------------------	-----

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Connector Lock	With
-----------------------	------

Mounting Angle	Straight
----------------	----------

Mating Connector Lock Type	Jackscrews
----------------------------	------------

Jackscrew Material	Zinc Alloy
--------------------	------------

Wire Insulation Support	With
-------------------------	------

PCB Mount Retention Type	None
--------------------------	------

Screw & Hole Thread Size	4-40
--------------------------	------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Enclosure	With
-----------	------

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------



Dimensions

Cable Outside Diameter	4.83 – 9.53 mm [.19 – .375 in]
Cable Insulation Diameter Range	4.83 – 9.53 mm [.19 – .375 in]
Accepts Cable Diameter (Max)	9.53 mm [.375 in]
Accepts Wire Insulation Diameter Range	1.52 mm [.06 in]
Solid Wire Size	.13 – .32 mm ²
Wire Size	.15 – .4 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Shielded	Yes
Circuit Application	Signal

Industry Standards

Insert Flammability Rating	UL 94V-0
----------------------------	----------

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Other

Comment	Maximum cable diameter after jacket and braid removed., There is a maximum Cable O.D. of 9.02 [.355] for Shielding Enclosure Expansion Tool 58241-4.
---------	--

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

Also in the Series | **AMPLIMITE HDE**



Crimp D-Sub Connectors(1)



D-Sub Connector Contacts(13)



IDC D-Sub Connectors(75)



Insertion & Extraction Tools(2)

Documents

Product Drawings

[KIT,RCPT,9P,HDE,SHLD ENCLSRE](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-747943-6_N.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-747943-6_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-747943-6_N.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English



Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English

[UL Report](#)

English