




TE Internal #: 2007262-1
SFP, SFP+ & zSFP+, Cage Assembly, Data Rate (Max) 16 Gb/s,
External Springs, SFP+, With Lightpipe, 1 x 2, Dual Round,
Standard, Standard
[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP, SFP+ & zSFP+



Pluggable I/O Product Type: **Cage Assembly**
Data Rate (Max): **16 Gb/s**
EMI Containment Feature Type: **External Springs**
Pluggable I/O Applications: **SFP+**
Lightpipe Options: **With Lightpipe**

Features

Product Type Features

Form Factor	SFP+
Cage Type	Ganged
Pluggable I/O Product Type	Cage Assembly
Lightpipe Options	With Lightpipe
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Port Matrix Configuration	1 x 2
Lightpipe Configuration	Dual Round
Lightpipe Style	Standard
Lightpipe Profile	Standard
Number of Ports	2

Electrical Characteristics

--	--



Data Rate (Max)	16 Gb/s
-----------------	---------

Termination Features

Termination Post & Tail Length	2.05 mm[.081 in]
Termination Method to Printed Circuit Board	Through Hole - Press-Fit

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Dimensions

PCB Thickness (Recommended)	2.25 mm[.089 in]
-----------------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Heat Sink Compatible	No
For Use With Pluggable I/O Products	SFP+ SMT Connector
Pluggable I/O Applications	SFP+
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tray, Package
------------------	---------------------

Other

EMI Containment Feature Type	External Springs
------------------------------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)



Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-SF59-C76264 SFP Connectors	 TE Part # CAT-C11-H50626 SFP+ to SFP+ I/O Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG
 TE Part # 2334985-2 SFP28 DIRECT ATTACH CA, 1M, 32AWG	 TE Part # CAT-C11-N4901114 SFP28 to SFP28 Cable Assembly: 30 AWG	 TE Part # CAT-C11-N49011 SFP28 to SFP28 Cable Assembly: 26 AWG	 TE Part # CAT-Q17-N49011 QSFP56-Four SFP56 Cable Assembly: 30 AWG
 TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG	 TE Part # 4-2821222-5 SFP56 DIRECT ATTACH CA, 2M, 30AWG	 TE Part # 4-2821224-5 SFP56 DIRECT ATTACH CA, 3M, 26AWG	 TE Part # 4-2334985-2 SFP56 DIRECT ATTACH CA, 1M, 32AWG



 TE Part # 1367147-1 SFP COVER, UNPLATED	 TE Part # 1367147-3 SFP COVER, UNPL, NO LOGO	 TE Part # 1761394-1 DUST COVER, SFP, GANGED & STACKED	 TE Part # CAT-SF59-AC229 SFP accessories
 TE Part # CAT-C11-H5 SFP+ to SFP+ I/O Cable Assembly: 24 AWG	 TE Part # CAT-C11-H506 SFP+ to SFP+ I/O Cable Assembly: 26 AWG	 TE Part # CAT-C11-H5062 SFP+ to SFP+ I/O Cable Assembly: 28 AWG	 TE Part # 2018002-3 SEATING TOOL, 1X2 KIT

Documents

Product Drawings

SFP+ 1x2 Cage Assembly, Light

English

CAD Files

Customer View Model

ENG_CVM_CVM_2007262-1_C.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2007262-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2007262-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1773408-1 Pluggable Input/Output Solutions catalog - SFP+ section

English

SFP+ Product Family: Cages, Connectors, Cable Assemblies 4-1773449-5

English

4-1773455-3 - Quick Reference Guide SFP+ Solutions

English

Product Specifications



Application Specification

English

Product Environmental Compliance

MD_2007262-1_02202017356_dmtec

English

MD_2007262-1_02202017356_dmtec

English