




Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Hardware Type: **Pin Hood**

Pin Hood Type: **External Closed End**

Connector System: **Wire-to-Wire**

Number of Positions: **12, 28, 75**

Sealable: **No**

Features

Product Type Features

Strain Relief	Without
Product Type	Hardware
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	12, 28, 75
---------------------	------------

Body Features

Material	Carbon Steel
----------	--------------

Contact Features

Pin Hood Type	External Closed End
---------------	---------------------

Mechanical Attachment

Hardware Type	Pin Hood
---------------	----------

Connector Mounting Type

Cable Mount (Free-Hanging)

Dimensions

Width

36.12 mm[1.422 in]

Height

72.26 mm[2.845 in]

Length

17.45 mm[.687 in]

Usage Conditions

Operating Temperature Range

-55 – 150 °C[-67 – 302 °F]

Operation/Application

For Use With

75-Position Standard & Posted Connectors

Circuit Application

Power & Signal

Packaging Features

Packaging Quantity

100

Packaging Method

Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | NECTOR M Series



Circular Connector Hardware(1)



Plug & Socket Lighting Connector Accessories(1)



Rectangular Connector Hardware(13)



Rectangular Power Connectors(2)



Standard Circular Connectors(124)

Documents

Product Drawings

75 PL. EXTERNAL PIN HOOD

English

CAD Files

Customer View Model

[ENG_CVM_CVM_201368-4_T.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_201368-4_T.3d_stp.zip](#)

English



Customer View Model

[ENG_CVM_CVM_201368-4_T.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[PIN HOODS FOR AMP SERIES "M" AND MINIATURE DUALATCH CONNECTOR BL](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[75 and 104 Position Series "M" Connectors and Accessories](#)

English

Agency Approvals

[Agency Approval Document](#)

English