

201786-4 ✓ ACTIVE

NECTOR | NECTOR M Series


TE Internal #: 201786-4

Rectangular Connector Hardware, Pin Hood, Internal Open End,
Wire-to-Wire, 34 Position, Wire & Cable, Power & Signal, NECTOR
M Series

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Hardware Type: **Pin Hood**

Pin Hood Type: **Internal Open End**

Connector System: **Wire-to-Wire**

Number of Positions: **34**

Sealable: **No**

Features

Product Type Features

Strain Relief	Without
Product Type	Hardware
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	34
---------------------	----

Body Features

Material	Carbon Steel
----------	--------------

Contact Features

Pin Hood Type	Internal Open End
---------------	-------------------

Mechanical Attachment

Hardware Type	Pin Hood
---------------	----------



Connector Mounting Type

Cable Mount (Free-Hanging)

Dimensions

Width

22.41 mm[.882 in]

Height

50.8 mm[1.999 in]

Length

18.26 mm[.719 in]

Usage Conditions

Operating Temperature Range

-55 – 150 °C[-67 – 302 °F]

Operation/Application

For Use With

16-Position Mixed Connectors, 20 Position High Voltage Connectors, 34-Position Posted Connectors, 34-Position Standard Connectors

Circuit Application

Power & Signal

Packaging Features

Packaging Quantity

100

Packaging Method

Bag

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: JUNE 2022 (224)
 Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | NECTOR M Series



Circular Connector Hardware(1)



Plug & Socket Lighting Connector Accessories(1)



Rectangular Connector Hardware(13)



Rectangular Power Connectors(2)



Standard Circular Connectors(124)

Documents

Product Drawings

34 PL. PIN HOOD

English

CAD Files

Customer View Model

[ENG_CVM_201786-4_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_201786-4_D.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_201786-4_D.2d_dxf.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_CVM_201786-4_L.3d_igs.zip](#)



English

Customer View Model

[ENG_CVM_CVM_201786-4_L.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_201786-4_L.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[PIN HOODS FOR AMP SERIES "M" AND MINIATURE DUALATCH CONNECTOR BL](#)

English

Agency Approvals

[Agency Approval Document](#)

English