



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > LVDS Connectors (LCEDI)



Number of Positions: **30**

Centerline (Pitch): **.5 mm [.02 in]**

Mated Height: **1.1 mm [.043 in]**

LVDS Connector Product Type: **Pull Bar**

Features

Product Type Features

LVDS Connector Product Type	Pull Bar
-----------------------------	----------

Configuration Features

Number of Positions	30
---------------------	----

Body Features

Shell Base Material	Stainless Steel
---------------------	-----------------

Housing Features

Centerline (Pitch)	.5 mm [.02 in]
--------------------	----------------

Dimensions

Mated Height	1.1 mm [.043 in]
--------------	------------------

Industry Standards

Approved Standards	VESA
--------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2018 (191)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | LCEDI



LVDS Connectors (LCEDI)(6)

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_2023348-2_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2023348-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2023348-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[7-1773457-2_LCEDI/LCEDI_SR_QUICK_REFERENCE_GUIDE](#)

English

Product Specifications

[LCEDI CONNECTOR PRODUCT SPECIFICATION](#)

Japanese

[Product Specification](#)

Japanese

Product Environmental Compliance

[TE Material Declaration](#)

English