




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**  
Connector & Housing Type: **Receptacle**  
Connector System: **Wire-to-Board**  
Number of Positions: **6**  
Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

|                                   |               |
|-----------------------------------|---------------|
| Connector Product Type            | Housing       |
| Connector & Housing Type          | Receptacle    |
| Connector System                  | Wire-to-Board |
| Connector & Contact Terminates To | Wire & Cable  |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Positions | 6 |
| Number of Rows      | 1 |

Electrical Characteristics

|                                       |         |
|---------------------------------------|---------|
| Termination Resistance                | 12 mΩ   |
| Insulation Resistance                 | 5000 MΩ |
| Dielectric Withstanding Voltage (Max) | 750 V   |
| Operating Voltage                     | 250 VAC |

Contact Features

|                              |                  |
|------------------------------|------------------|
| Contact Layout               | Inline           |
| Contact Type                 | Socket           |
| Contact Base Material        | Beryllium Copper |
| Contact Current Rating (Max) | 3 A              |

Termination Features



|                                    |       |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

Mechanical Attachment

|                  |         |
|------------------|---------|
| Strain Relief    | Without |
| Mating Retention | Without |

Housing Features

|                             |                  |
|-----------------------------|------------------|
| Housing Entry Configuration | Both Ends Closed |
| Housing Material            | Thermoplastic    |
| Centerline (Pitch)          | 2.54 mm[.1 in]   |
| Housing Color               | Black            |

Dimensions

|                    |                  |
|--------------------|------------------|
| Connector Length   | 15.37 mm[.61 in] |
| Connector Height   | 3.55 mm[.14 in]  |
| Row-to-Row Spacing | 2.54 mm[.1 in]   |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -65 – 105 °C[-85 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                     |        |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

Industry Standards

|                        |                               |
|------------------------|-------------------------------|
| Glow Wire Rating       | Standard Part - Not Glow Wire |
| Approved Standards     | CSA LR7189, UL E28476         |
| UL Flammability Rating | UL 94V-0                      |

Packaging Features

|                    |         |
|--------------------|---------|
| Packaging Quantity | 1       |
| Packaging Method   | Package |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                              |
|-----------------------------------------------|----------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                    |
| EU ELV Directive 2000/53/EC                   | Compliant                                    |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold      |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224) |



Candidate List Declared Against: JAN 2021  
(211)  
Does not contain REACH SVHC

|                           |                                                        |
|---------------------------|--------------------------------------------------------|
| Halogen Content           | BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources. |
| Solder Process Capability | Not applicable for solder process capability           |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                        |                                                           |                                                         |                                                   |
|--------------------------------------------------------|-----------------------------------------------------------|---------------------------------------------------------|---------------------------------------------------|
| <br>TE Part # 87666-2<br>MOD IV RECP PLTD 30 SEL       | <br>TE Part # 6-87756-7<br>MOD IV REC STP INT'L SPEC REEL | <br>TE Part # 87756-6<br>MOD IV RECP PLTD SN            | <br>TE Part # 87809-1<br>MOD V RECP PLTD 30 AU    |
| <br>TE Part # 6-87756-2<br>MOD IV RECP PLTD 15 DPLX LF | <br>TE Part # 87309-9<br>MOD V RECP PLTD 30 AU            | <br>TE Part # 87523-5<br>MOD IV RECP PLTD SN            | <br>TE Part # 102548-5<br>MOD IV RECP PLTD 30 SEL |
| <br>TE Part # 87309-8<br>MOD V RECP PLTD SN            | <br>TE Part # 2-87523-3<br>MOD IV RECP PLTD 15 DPLX       | <br>TE Part # 5-103171-4<br>MOD IV RECP PLTD 30 DPLX LF | <br>TE Part # 85969-8<br>MOD IV RECP PLTD 30 SEL  |



TE Part # 87666-3  
MOD IV RECP PLTD SN

TE Part # 5-102920-1  
MOD IV RECP PLTD 30 DPLX LF

TE Part # 103455-1  
MOD V RECP PLTD 30 AU

TE Part # 102316-6  
MOD IV RECP PLTD 15 DPLX

TE Part # 2-87195-4  
MOD IV RECP PLTE 15 DPLX

TE Part # 102917-5  
MOD IV RECP PLTD 15 SEL

Also in the Series | AMPMODU IV/V

Automotive Housings(2)

Backplane Connector Housings(1)

Board-to-Board Connector Contacts(6)

Insertion & Extraction Tools(4)

PCB Connector Covers(18)

PCB Connector Keying(6)

PCB Connector Mounting(1)

PCB Connector Strain Relief(3)

PCB Headers & Receptacles(939)

PCB Latches, Locks & Retainers(7)

Rectangular Connector Housings(5)

Standard Rectangular Connectors(8)



Wire-to-Board Connector Assemblies & Housings(467)



Wire-to-Board Connector Contacts (326)

Documents

Product Drawings

06 MODIV HSG SR MRKD .100CL

English

CAD Files

3D PDF

English

Customer View Model

ENG\_CVM\_1-87499-1\_T.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_1-87499-1\_T.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_1-87499-1\_T.3d\_stp.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-87499-1\_AN.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-87499-1\_AN.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-87499-1\_AN.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU\_INTERCONNECTION\_SYSTEM\_SECTION5\_CONT

English

Product Specifications

Application Specification



English

[Product Environmental Compliance](#)

[TE Material Declaration](#)

English