



AMP

TE Internal #: 205282-1

Rack & Panel Covers & Plugs, Dust Cover, Plug, Vinyl, Cable-to-Panel, Sealable, Wire & Cable, Cable Mount (Free-Hanging), -85 – 257 °F [-65 – 125 °C]

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > Rack & Panel Backplane > Rack & Panel Covers & Plugs



Protection & Strain Relief Accessory Type: **Dust Cover**

Compatible With Connector Style: **Plug**

Primary Product Material: **Vinyl**

Connector System: **Cable-to-Panel**

Sealable: **Yes**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Dust Cover
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Body Features

Primary Product Material	Vinyl
--------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Usage Conditions

Compatible With Connector Style	Plug
Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]

Packaging Features

Packaging Method	Package
------------------	---------

Other

Comment	For A404
---------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Documents

Product Drawings

DUST CAP FOR PLUG

English

CAD Files

Customer View Model

[ENG_CVM_205282-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_205282-1_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_205282-1_B.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



ARINC 600 Next Generation Receptacle Connector

English