



Buchanan WireMate

TE Internal #: 2008552-3

Ballast Connectors, Connector, Poke-In, Header, Wire-to-Board, 3 Position, .323 in [8.2 mm] Centerline, Printed Circuit Board, 18 AWG Wire Size, Power

[View on TE.com >](#)

Connectors > Lighting Connectors > Ballast Connectors



Lighting Product Type: **Connector**

Termination Method to Wire & Cable: **Poke-In**

Lighting Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Features

Product Type Features

Strain Relief	Without
Make First / Break Last	No
Wire/Cable Type	Discrete Wire
Connector Style	Screwless Wire
Glow Wire Rating	Standard Part - Not Glow Wire
Lighting Product Type	Connector
Lighting Connector Type	Header
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Pre-Designed Cables Available	No
Number of Rows	1
Preloaded	Yes



Number of Positions	3
---------------------	---

Electrical Characteristics

Operating Voltage (Max)	600 VDC
-------------------------	---------

Body Features

Header Mating Direction	Vertical
-------------------------	----------

Contact Features

Contact Termination Area Plating Finish	Matte
---	-------

Stamped and Formed	Yes
--------------------	-----

Contact Termination Area Plating Material	Tin
---	-----

Contact Termination Area Plating Thickness	3.05 μm [120 μin]
--	--

Contact Layout	Inline
----------------	--------

Contact Mating Area Plating Material	Tin
--------------------------------------	-----

Contact Mating Area Plating Thickness	2.03 – 3.05 μm [79.92 – 120.08 μin]
---------------------------------------	--

Contact Mating Area Plating Material Finish	Matte
---	-------

Contact Current Rating (Max)	6 A
------------------------------	-----

Termination Features

Tool-less Wire Termination	Yes
----------------------------	-----

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Termination Method to Wire & Cable	Poke-In
------------------------------------	---------

Mechanical Attachment

Mounting Angle	Vertical
----------------	----------

PCB Mount Alignment	With
---------------------	------

PCB Mount Retention	With
---------------------	------

PCB Mount Retention Type	Boardlock
--------------------------	-----------

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Color	Black
---------------	-------

Housing Material	PBT GF
------------------	--------

Centerline (Pitch)	8.2 mm[.323 in]
--------------------	-----------------

Dimensions

Width	7.35 mm[.289 in]
-------	------------------

Length	25 mm[.984 in]
--------	----------------



Height	13 mm[.512 in]
PCB Thickness (Recommended)	1.8 mm[.07 in]
Post-Mating Assembly Measurement	25 mm[.984 in]
Accepts Wire Insulation Diameter Range	2.2 mm[.087 in]
Wire Size	18 AWG

Usage Conditions

UV Exposure Rated	No
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

Industry Standards

UL Flammability Rating	UL 94V-0
Agency/Standard	CSA, UL
Agency/Standard Number	C22.2 No. 182.3, UL 1977

Packaging Features

Packaging Method	Box & Tray, Tray
------------------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

[ASSY, IN-LINE VERT SCREWLESS WIRE](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2008552-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2008552-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2008552-3_A.3d_stp.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_2008552-3_A2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_2008552-3_A2.3d_stp.zip](#)



English

Customer View Model

[ENG_CVM_2008552-3_A2.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Vertical and In-Line Screwless Wire Connectors

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Agency Approvals

UL Report

English