

205842-1 ✓ ACTIVE

AMP | AMP CPC

TE Internal #: 205842-1

Circular Power Connectors, Housing, 250 VDC, Wire-to-Wire, 63 Position, Wire & Cable, Plug, Socket, Signal, Black, All Plastic, Thermoplastic, AMP CPC

[View on TE.com >](#)



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Connector Product Type: **Housing**

Operating Voltage: **250 VDC**

Connector System: **Wire-to-Wire**

Number of Positions: **63**

Sealable: **No**

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Plug
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	63
Number of Power Positions	0
Number of Signal Positions	63

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features



Reverse Gender	No
Contact Type	Socket
Contact Current Rating (Max)	7.5 A
Contact Protection	With

Mechanical Attachment

Panel Mount Feature Type	Flange
Screw & Hole Thread Size	1-3/8 - 18 UNEF-2A
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Alignment	With
Mating Retention	With
Panel Mount Feature	Without
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling

Housing Features

Body Orientation	Straight
Housing Color	Black
Housing Material	Thermoplastic
Circular Connector Shell Size	23

Dimensions

Accepts Wire Insulation Diameter Range	1.73 mm[.068 in]
--	------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
VDE Tested	No

Packaging Features

Packaging Method	Bag
Packaging Quantity	100



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer











This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

<p>TE Part # CAT-AM71-C83998M CPC Connectors, Series 2</p>	<p>TE Part # CAT-AM71-C83998E Connectors with Posted Contacts, CPC Series 2</p>	<p>TE Part # 5-2407269-1 CAP, CPC, SIZE 23 PLUG, ORANGE</p>	<p>TE Part # 5-2407269-2 CAP, CPC, SIZE 23 PLUG, BLACK</p>



Also in the Series | AMP CPC



Documents

Product Drawings

CPC PLUG ASSEMBLY SIZE 23-63

English

CAD Files

3D PDF

English

Customer View Model



[ENG_CVM_205842-1_J.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_205842-1_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_205842-1_J.3d_stp.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_205842-1_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_205842-1_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_205842-1_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP Circular Connectors for Commercial Signal & Power Applications](#)

English

Product Specifications

[Connector, Circular Plastic](#)

English

[Product Specification](#)

English

[Product Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[CSA Certificate](#)

English